

TECHNICAL DATA SHEET

Description: 1.0mm C-Clip for RF contacts

PART NUMBER: W9908

Series: Contact clip



Features:

- PWB Footprint 3.2 x 1.7 mm
- Nominal Contact Height 1 mm
- Tape & Reel Packaging
- RoHS Compliant Product

Applications:

Antenna Contacts

All dimensions are in mm / inches

Issue: 1941

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: 1.0mm C-Clip for RF contacts

Series: Contact clip

PART NUMBER: W9908

MECHANICAL SPECIFICATIONS

Length	3.41 mm
Width	1.50 mm
Height (decompressed)	1.45 mm
Nominal compressed height	1.00 mm

Weight 0.1 g

Material Stainless steel,

Thickness 0.12±0.01 mm

Plating Ni+Au all over

Ni: $0.75\pm0.5~\mu m$

Au: (Hard gold) 0.5 µm min.

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40 to +85 ° C
Storage Temperature -40 to +85 ° C
RoHS Compliant Yes










Series: Contact clip


PART NUMBER: W9908

MECHANICAL DRAWING









Recommended pick and place area: less than Ø1.2mm.







Series: Contact clip

PART NUMBER: W9908

OTHER SPECIFICATIONS

1.PWB Layouts:










Series: Contact clip

PART NUMBER: W9908

OTHER SPECIFICATIONS

2.PWB Footprint Dimensions and C-Clip Position for W9908

Pad dimensions:








Series: Contact clip

PART NUMBER: W9908

OTHER SPECIFICATIONS

C-clip position on PWB layout:








Series: Contact clip

PART NUMBER: W9908

OTHER SPECIFICATIONS

3. Ground Clearance Area for W9908 C-Clip:







Series: Contact clip

PART NUMBER: W9908


Recommendation for reflow soldering process

Printing stencil thickness 0.15 to 0.25 mm is recommended for the solder paste.

The maximum soldering temperature should not exceed 260° C.

The temperature profile recommendations for reflow solder process are presented in Figure 1 & 2. The reflow profile presented in Figure 2 describes maximum reflow temperatures.

	Method of heat transfer	Controlled hot air convection	$]^{ri}$
1	Average temperature gradient in preheating	2.5°C/s	
2	Soak time	2-3 minutes	
3	Max temperature gradient in reflow	3°C/s	
4	Time above 217°C	Max 30 sec	
5	Peak temperature in reflow	230°C for 10 seconds	
6	Temperature gradient in cooling	Max -5°C/s	



Issue:






Series: Contact clip

PART NUMBER: W9908

Recommendation for reflow soldering process

Figure 2 - Maximum temperature profile recommendation for reflow soldering process

	Method of heat transfer	Controlled hot air convection
1	Average temperature gradient in preheating	2.5°C/s
2	Soak time	2-3 minutes
3	Max temperature gradient in reflow	3°C/s
4	Time above 217°C	Max 60 sec
5	Time above 230°C	Max 50 sec
6	Time above 250°C	Max 10 sec
7	Peak temperature in reflow	260°C for 5 seconds
8	Temperature gradient in cooling	Max -5°C/s



Issue: 1941

ROHS






Series: Contact clip

PART NUMBER: W9908

PACKAGING

Tape & reel. Packaging unit: 2,500 pcs per reel, 1,5000 pcs per box.



Issue: 1941

ROHS