



PART NUMBER: W5084x

Series: OMNI Antenna



Features:

- 698-3700MHz
- Omni radiation pattern in horizontal plane
- Gain 2/4 dBi
- Power rating 5W
- IP65
- Connector options:
 - W5084 TNC male
 - W5084K SMA male

Applications:

- LTE radios
- 2G/3G/4G radios
- Gateways, Routers, Set top boxes, Security, Metering
- IoT, M2M
- Optimized for straight and 90deg bent positions

All dimensions are in mm / inches

Issue: 1823

In the effort to improve our products, we reserve the right to make changes judged to be necessary. $\texttt{CONFIDENTIAL} \ \texttt{AND} \ \texttt{PROPRIETARY} \ \texttt{INFORMATION}$

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 12220 World Trade Drive San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: LTE 698-3700MHz Swivel Dipole

Series: OMNI Antenna

PART NUMBER: W5084x

ELECTRICAL SPECIFICATIONS

Frequency	698-960/1400-	2690/3400-3	700MHz
Nominal Impedance	ļ	50	Ω
*VSWR(698-960MHz/1400-2690MHz)		3	Max
*VSWR(3400-3700MHz)	;	3.6	Max
**VSWR(698-960/1400-2690/3400-3700N	ИHz)	3	Max
Average Efficiency(698-960MHz)		58	%
Average Efficiency(1400-2690MHz)		78	%
Average Efficiency(3400-3700MHz)		60	%
Peak Gain (698-960MHz)		2	dBi +/- 1 dB
Peak Gain (1400-2690MHz)		4	dBi +/- 1 dB
Peak Gain (3400-3700MHz)		5	dBi +/- 1 dB
Polarization:	Ve	ertical	
Power withstanding		5	W
Connector type	TNC male	(SMA male i	s optional)
Connector Options	W5084	TNC male	connector
	W5084K	SMA male	connector



^{*}VSWR spec only for W5084 TNC male connector version

^{**}VSWR spec only for W5084K SMA male connector version



TECHNICAL DATA SHEET

Description: LTE 698-3700MHz Swivel Dipole

Series: OMNI Antenna

PART NUMBER: W5084x

MECHANICAL SPECIFICATIONS

Plastic radome ABS/PC

Color Black

Flammability UL94-V0

Ingress Protection IP65

Weight 65.9 g

Overall Length(W5084/W5084K) 228.84/223.24mm [9.01/8.79INCHES]

Position 0°, 45° & 90°

ENVIRONMENTAL SPECIFICATIONS

Operating temperature -40/+85 ° C

Storage Temperature -40/+85 ° C

Salt mist 96 hours






Series: OMNI Antenna


PART NUMBER: W5084x

MECHANICAL DRAWING

W5084 TNC male connector



W5084K SMA male connector



Issue: 1823

RoHS






Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS

VSWR








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS

Efficiency








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS

Peak Gain








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS










Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS



Issue: 1823

ROHS






Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS










Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS










Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS








Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS










Series: OMNI Antenna

PART NUMBER: W5084x

CHARTS







TECHNICAL DATA SHEET

Description: LTE 698-3700MHz Swivel Dipole

Series: OMNI Antenna

PART NUMBER: W5084x

PACKAGING

1PCS/PE bag 100PCS/Carton box

