

Han HPR HPTC 400 CS UNSH IP65/67 95



Image is for illustration purposes only. Please refer to product description.

Part number	10 40 271 2125
Specification	Han HPR HPTC 400 CS UNSH IP65/67 95
HARTING eCatalogue	https://b2b.harting.com/10402712125

Identification

Category	Connector sets
Series of hoods/housings	Han® HPR HPTC
Type of hood/housing	Complete set
Description of hood/housing	Cable side With integrated cable gland
Type of cable	Copper cable (round)
Features	for stranded wires according to IEC 60228 Class 5

Version

Size	2
Shielding	360° shielding
Coding	16 coding options
Cable entry	1x M25
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Conductor cross-section	95 mm²
Rated current	400 A
Rated voltage	1,800 V
Rated impulse voltage	10 kV
Pollution degree	4
Overvoltage category	III
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥25
Degree of protection acc. to IEC 60529	IP65 IP67
Clamping range	14.5 ... 18 mm

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Aluminium die-cast Corrosion resistant
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	4141b1b0-d696-48fb-8ad9-5046cd2452df
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	EN 50467 EN 50124-1 IEC 61373 Category 1 Class B EN 45545 EN 60137
----------------	--

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440101 Rectangular connectors (set)