

790 MHz - 960 MHz / 1710 MHz - 2170 MHz / 2300 MHz - 2700 MHz, 11 dBi, Log Periodic Antenna, V-pol, High Gain, Type N Female Connector

LCANLP1006

Features

- Frequency coverage for 790 MHz to 2700 MHz
- · Very High Gain 11 dBi Directional Antenna
- · Each connector covers wide band of frequencies
- Easy Install universal mounting bracket provided
- · Weatherproof ABS radome
- Pigtail 12 inches
- N-Type Female connector

Applications

- Point-to-point, LPWAN, LoRA, LTE-M, NB-IoT, IoT, M2M applica DAS (Distributed Antenna Systems)
- 5G / 4G LTE B1 to B21, B23, B24, B25 / 3G / GSM / AWS / WLAN operation supported
- · 5G Bands supported

- IEEE 802.11a / b /g / n / ac / ad / ah/ ax Wi-Fi applications
- · Public safety, utilities, CCTV and local radio coverage
- Smart cities expansion for coverage and IOT / IIOT

Description

The L-com LCANLP1006 is a high performance, wideband log periodic antenna designed to operate from 790 to 2700 MHz for point to point communications. The LCANLP1006 from L-com has 10 to 11 dbi of gain and can be used for long distance directional communication over a wide range of frequencies. The LCANLP1006 is ideal for boosting 5G, LTE, CMDA, LoRA, IoT, WI-FI

The log periodic LCANLP1006 has 47 vertical beamwidth and 58 horizontal beamwidth. This antenna has Vertical polarization and the included mounting brackets allow for either vertical or horizontal mounting configurations. Log periodic antennas function as boosters where the existing cellular signal is weak and needs to reach further distances. The L-com directional antenna has a 12 inches long pigtail terminated with 1 Type N Female connector.

L-com's 790 to 2700 MHz log periodic LCANLP1006 antenna with 11 dBi max gain for sub 6 GHz 5G DAS networks operates in bands n1, n2, n3, n5, n7, n8, n18, n20, n25, n26, n30, n34, n38, n39, n40, n41, n53, n65, n66, n67, n70, n80, n81, n82, n84, n86, n89, n90, n91, n92, n93, n94, n95, n97, n98. This 5G directional log periodic antenna with N Female Type connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

Configuration

Design Band Type Radiation Pattern Polarization Cable Type Cable Length Connector Type Number of Ports

Log Periodic Multi Directional Vertical Coax Cable 11.81 in [299.97 mm] N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR		1.5:1	1.7:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 790 MHz - 960 MHz / 1710 MHz - 2170 MHz / 2300 MHz - 2700 MHz, 11 dBi, Log Periodic Antenna, V-pol, High Gain, Type N Female Connector



790 MHz - 960 MHz / 1710 MHz - 2170 MHz / 2300 MHz - 2700 MHz, 11 dBi, Log Periodic Antenna, V-pol, High Gain, Type N Female Connector



LCANLP1006

Impedance		50		Ohms
Gain	10		11	dBi
Front to Back Ratio	25			dB
Input Power			100	Watts

Specifications by Band

		Band 3	Band 4	Band 5	Units
0.79 to 0.96	1.71 to 2.17	2.3 to 2.7			GHz
10	10.5	11			dBi
58	55	51			Degrees
47	46	42			Degrees
25	25	25			dB
1.7:1	1.5:1	1.5:1			
100	100	100			Watts
	10 58 47 25 1.7:1	10 10.5 58 55 47 46 25 25 1.7:1 1.5:1	10 10.5 11 58 55 51 47 46 42 25 25 25 1.7:1 1.5:1 1.5:1	10 10.5 58 55 47 46 25 25 1.7:1 1.5:1 1.5:1	10 10.5 11 58 55 51 47 46 42 25 25 25 1.7:1 1.5:1 1.5:1

Mechanical Specifications

Radome Material ABS

Size

 Length
 17.4 in [441.96 mm]

 Width
 8.3 in [210.82 mm]

 Height
 2.5 in [63.5 mm]

 Weight
 2.2 lbs [997.9 g]

Environmental Specifications

Temperature

Operating Range -40 to +65 deg C
Wind Survivability 130.5 MPH [210.02 KPH]
Wind Loading 23.5 lbs at 100 MPH
36.2 lbs at 125 MPH

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

790 MHz - 960 MHz / 1710 MHz - 2170 MHz / 2300 MHz - 2700 MHz, 11 dBi, Log Periodic Antenna, V-pol, High Gain, Type N Female



790 MHz - 960 MHz / 1710 MHz - 2170 MHz / 2300 MHz - 2700 MHz, 11 dBi, Log Periodic Antenna, V-pol, High Gain, Type N Female Connector

LCANLP1006

Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

