

## Coaxial PCB Connector 82\_QLA-01-0-2/112\_N

### Description

Straight PCB jack

Interface Standards  
NIM-CAMAC-Standard CD/N549



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 1.4 GHz

#### Mechanical Data

Board mounting type through holes  
Weight 0.0033 kg

#### Environmental Data

Operating temperature -55 °C to 150 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing DCA-00012933  
Mounting hole DOU-00012844

### Ordering Information

Single package 82\_QLA-01-0-2/112\_NE

### Remarks

PCB connector without stand-offs