

## Coaxial PCB Connector 90\_MMCX-S50-0-55/119\_O

### Description

Straight PCB jack

Interface Standards  
SUHNER-MMCX



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Board mounting type	surface mount
Weight	0.0002 kg

#### Environmental Data

Operating temperature	-40 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating
Outer contact	Brass	Gold Plating
Body	LCP (Liquid crystal polymer)	

### Related Documents

Outline drawing	DOU-00080379
Mounting hole	DOU-00012840

### Ordering Information

Single package	90_MMCX-S50-0-55/119_OE
Bulk 100 pcs package	90_MMCX-S50-0-55/119_OH