



**BF2** Fuses

# **BF2 Fuses Rated 32V**

This BF2 fuse is rated at 32V and offers a bolt-on fuse for high current wiring protection. Current rating 100A - 500A; with transparent housing material for easy detection of blown fuses.

## **Specifications**

Voltage Rating: Interrupting Ratings:

**Recommended Environmental Temperature:** Terminals Material: Housing Material: Clear Housing Material: Mounting Torque M8: Mounting Torque M6: Refers to:

32 VDC 100A - 300A: 2000A @ 32 VDC 400A - 500A: 1500A @ 32 VDC -40°C to + 125°C Tin plated copper alloy PET-GF33 (U.L. 94 Flammability rating - V0) PES (U.L. 94 Flammability rating - V0) 12.0 Nm +/- 1Nm 6.0 Nm +/- 1Nm ISO 8820-5:2015, UL 248 Special Purpose




## **Ordering Information**

Part Number	Rating	Package Size		
Standard M8 Holes				
153.5395.xxxx	100 - 500	200		
M6 Holes				
153.7011.xxxx	100 - 500	200		

### **Time Current Characteristics**

% of Rating	Opening Time Min / Max (s)			
/o or nating	100A - 250A	300A - 500A		
75	- / -	14,400 / ∞		
100	14,400 / ∞	-/-		
135	120 / 1,800	- / -		
200	1 / 15	1 / 15		
350	0.3 / 5	0.5 / 5		
600	0.1 / 1	0.1 / 1		

## **Time-Current Characteristic Curves**



### Ratings

Part Number	Current Rating (A)	Housing Color	Test Cable Size (mm²)	Typ. Voltage Drop (mV)	Typ. Cold Resistance (mΩ)	Typ. l²t (A²s)
153.xxxx.6102	100		16	102	0.70	46,800
153.xxxx.6122	125		25	81	0.52	118,100
153.xxxx.6152	150		25	77	0.42	113,400
153.xxxx.6172	175		25	104	0.36	154,400
153.xxxx.6202	200		35	102	0.34	288,000
153.xxxx.6222	225		35	107	0.29	236,000
153.xxxx.6252	250		50	86	0.25	292,500
153.xxxx.63021	300		70	68	0.21	486,000
153.xxxx.64021	400		70	70	0.13	964,000
153.xxxx.65021	500		70	60	0.12	1,449,000

Note 1: Short Circuit Protector only

The typical I<sup>2</sup>t is an average value calculated from the breaking capacity tests by using the melting time before the arcing occurs.

### REV07272021

Littelfuse® products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littlefuse<sup>®</sup> product documentation. Warranties granted by Littlefuse<sup>®</sup> shall be deemed void for products used for any purpose not expressly set forth in applicable Littlefuse<sup>®</sup> documentation. Littlefuse<sup>®</sup> shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littlefuse<sup>®</sup> as set forth in applicable Littlefuse<sup>®</sup> documentation. The sale and use of Littlefuse<sup>®</sup> products is subject to Littlefuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse


# High Current Fuses



# **BF2** Fuse Rated 32V

### **Dimensions**

Dimensions in mm for reference only. See outline drawing for dimensions and tolerances




9.3 (100-200A)	0.5 (100-125A) 0.8 (150-200A)
9.4 (225-300A) 10 (400- 500A)	1.0 (225-300A) 1.5 (400-500A)

### **Typical Derating of Fuse Melting Element**

Temperature Security Margin is 20%

Please contact Littelfuse® for Details Regarding Derating Test Set-Up.



### **Temperature Table**

	max. allowed current load [A] at ambient temperature (typical derating)						
	-40°C	0°C	20°C	65°C	85°C	110°C	125°C
100A	100	96	91	76	69	58	50
125A	125	115	108	90	80	67	58
150A	150	138	130	109	99	83	73
175A	167	151	142	120	108	92	80
200A	189	171	161	135	122	103	90
225A	200	180	170	143	129	109	94
250A	250	250	244	200	177	145	123
300A	225	225	225	201	181	153	133
400A	300	300	300	262	236	198	172
500A	364	329	311	263	238	202	177

Derating curves may change depending on the final condition of the application (terminals characteristics, wire size etc..). Please ask Littelfuse for more information.

#### REV07272021

Littelfuse® products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse<sup>®</sup> product documentation. Warranties granted by Littelfuse<sup>®</sup> shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse<sup>®</sup> documentation. Littelfuse<sup>®</sup> shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse<sup>®</sup> documentation. Littelfuse<sup>®</sup> shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse<sup>®</sup> as set forth in applicable Littelfuse<sup>®</sup> documentation. The sale and use of Littelfuse<sup>®</sup> products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse®