Data Sheet



Coaxial Cable Connector 16_MMCX-50-2-4/111_O

Description

Right angle cable plug

Interface standards SUHNER-MMCX



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \, \Omega \\ \text{Interface frequency max.} & 6 \, \text{GHz} \end{array}$

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0009 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -55 °C to 155 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing DOU-00006003
Catalogue drawing DOU-00006005
Assembly instruction DOC-0000241539

Ordering Information

 Bulk 100 pcs package
 16_MMCX-50-2-4/111_OH

 Single package
 16_MMCX-50-2-4/111_OE

Additional Information

Suitable cables RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.