Data Sheet

HUBER+SUHNER

Coaxial PCB Connector 82_BNC-50-0-1/133_N

Description

Straight PCB jack

Interface Standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data		
Impedance	50 Ω	
Interface frequency max.	4 GHz	
Mechanical Data		
Board mounting type	through holes	
Weight	0.0053 kg	
Environmental Data		
Operating temperature	-65 °C to 165 °C	
2011/65/EU (RoHS - including	compliant	
2015/863 and 2017/2102)		
Material Data		
Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Related Documents		
Outline drawing	DOU-00013009	
Catalogue drawing	DCA-00013001	
Mounting hole	DOU-00012084	
Ordering Information		
Single package	82_BNC-50-0-1/133_NE	
Tray package	82_BNC-50-0-1/133_NH	
Remarks		

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.