


Unsheathed Fine Gage Thermocouples

Convenient Packages of 5

Shown smaller than actual size.




Important Ordering Notes

Base Metal Thermocouples

Prices given for 300 mm (12") lengths. Other sizes and lengths are available on special order. A 300 mm (12") length corresponds to a 600 mm (24") loop. To order longer lead lengths for base metal calibrations of 0.125 mm (0.005") or larger, additional cost per 300 mm (12") per package. Additional wire diameters are also available for Type N. Please check with Sales.

Platinum/Rhodium Thermocouples

Prices given for 150 mm (6") lengths. Other sizes and lengths are available on special order. A 150 mm (6") length corresponds to a 300 mm (12") loop. To order longer lead lengths for Pt/Rh calibrations, see the table (below right).



Base Metal Calibrations: 300 mm (12") Length Standard—Package of 5

Calibration	Wire Dia. mm (in)	Model Number
J Iron-Constantan	0.025 (0.001)	IRCO-001
	0.050 (0.002)	IRCO-002
	0.075 (0.003)	IRCO-003
	0.125 (0.005)	IRCO-005
	0.25 (0.010)	IRCO-010
	0.38 (0.015)	IRCO-015
	0.5 (0.020)	IRCO-020
	0.81 (0.032)	IRCO-032
T Copper-Constantan	0.025 (0.001)	COCO-001
	0.050 (0.002)	COCO-002
	0.075 (0.003)	COCO-003
	0.125 (0.005)	COCO-005
	0.25 (0.010)	COCO-010
	0.38 (0.015)	COCO-015
	0.5 (0.020)	COCO-020
	0.81 (0.032)	COCO-032
N OMEGA-P®-OMEGA-N®	0.075 (0.003)	OPON-003
	0.125 (0.005)	OPON-005
	0.25 (0.010)	OPON-010
	0.50 (0.020)	OPON-020
	0.81 (0.032)	OPON-032

Calibration	Wire Dia. mm (in)	Model Number
K CHROMEQA®-ALOMEGA®	0.013 (0.0005)†	CHAL-0005
	0.025 (0.001)	CHAL-001
	0.050 (0.002)	CHAL-002
	0.075 (0.003)	CHAL-003
	0.125 (0.005)	CHAL-005
	0.25 (0.010)	CHAL-010
	0.38 (0.015)	CHAL-015
	0.50 (0.020)	CHAL-020
	0.81 (0.032)	CHAL-032
	E CHROMEQA®-Constantan	0.013 (0.0005)†
0.025 (0.001)		CHCO-001
0.050 (0.002)		CHCO-002
0.075 (0.003)		CHCO-003
0.125 (0.005)		CHCO-005
0.25 (0.010)		CHCO-010
0.38 (0.015)		CHCO-015
0.50 (0.020)		CHCO-020
0.81 (0.032)		CHCO-032

† 0.013 mm (0.0005") diameter wires supplied with 200 mm (8") leads; maximum length 300 mm (12").
Note: Shorter lead is negative lead.

Pt/Rh Calibrations: 150 mm (6") Length Standard—Sold Individually

Calibration	Wire Dia. mm (in)	Model Number
R Pt/13%Rh-Pt	0.025 (0.001)	P13R-001
	0.050 (0.002)	P13R-002
	0.075 (0.003)	P13R-003
	0.125 (0.005)	P13R-005
	0.20 (0.008)	P13R-008
	0.25 (0.010)	P13R-010
	0.38 (0.015)	P13R-015
	0.50 (0.020)	P13R-020
	0.81 (0.032)	P13R-032

Calibration	Wire Dia. mm (in)	Model Number
S Pt/10%Rh-Pt	0.025 (0.001)	P10R-001
	0.050 (0.002)	P10R-002
	0.075 (0.003)	P10R-003
	0.125 (0.005)	P10R-005
	0.20 (0.008)	P10R-008
	0.25 (0.010)	P10R-010
	0.38 (0.015)	P10R-015
	0.50 (0.020)	P10R-020
	0.81 (0.032)	P10R-032

Pt/Rh Calibrations: 150 mm (6") Length Standard—Sold Individually

Calibration	Wire Dia. mm (in)	Model Number
B Pt/30%Rh-Pt/6%Rh-	0.20 (0.008)	P30R-008
	0.25 (0.010)	P30R-010
	0.38 (0.015)	P30R-015
	0.50 (0.020)	P30R-020
	0.81 (0.032)	P30R-032

SPECIAL SIZES, ALLOYS OR ASSEMBLIES
 Orders for special sizes, alloys or assemblies should be explicit and accompanied by a sketch or print, if possible.

Base metal thermocouples 0.125 mm (0.005") diameter and larger are made with Special Limits of Error wire.
 Thermocouple insulator model nos. SH, DH, FS and OV also featured in this section.
Note: Published price is based on market value at time of printing and is subject to change due to precious-metal market fluctuations.

For Pricing and Details Visit omega.com/thermocouples

Wire Dia. mm (inches)
0.025 (0.001")
0.050 (0.002")
0.075 (0.003")
0.125 (0.005")
0.20 (0.008")
0.25 (0.010")
0.38 (0.015")
0.50 (0.020")
0.81 (0.032")

Discount Schedule Base Metal Thermocouples	
1 to 10 pkgsNet
11 to 24 pkgs5%
25 to 49 pkgs10%
50 and up15%

Ordering Example: CHAL-005, package of five 300 mm (12") Type K thermocouples, 0.125 mm (0.005") diameter.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters