

Han® Board PCB 3+PE 7,62 PCB angled



•	
Part number	09 93 003 0300
Specification	Han® Board PCB 3+PE 7,62 PCB angled
HARTING eCatalogue	https://b2b.harting.com/09930030300

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han [®] Board
Element	Inserts
Description of the contact	Angled

Version

Termination method	Wave soldering termination
Gender	Male
Number of contacts	3
PE contact	Yes
Details	Please order coding pins separately.
Details	This contact insert is an unenclosed connector according to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.
	Contact inserts must not be coupled or decoupled under electrical load.
	Contact inserts must not be powered-up in the un-mated condition.

Technical characteristics

Contact spacing (mating side)	7.62 mm
Rated current	32 A
Rated current	The current-carrying capacity depends significantly on the printed circuit board used, the conductor cross-section used and the specific installation situation.
Rated voltage conductor-earth	480 V
Rated voltage conductor-conductor	830 V
Rated impulse voltage	6 kV

Page 1 / 3 | Creation date 2022-10-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Pushing Performance Since 1945

Technical characteristics

Pollution degree	2
Limiting temperature	-25 +125 °C -5 +65 °C While mating or unmating
Mating cycles	≥75
Degree of protection acc. to IEC 60529	IP20
PCB thickness	2.2 mm ±10 %
Material properties	
Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	80
Net weight	10.28 g
Country of origin	Germany
European customs tariff number	85340090
GTIN	5713140186712

Page 2 / 3 | Creation date 2022-10-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Commercial data


eCl@ss

27440205 Contact insert for industrial connectors

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (nonintermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2





Page 3 / 3 | Creation date 2022-10-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com