


PRODUCT DATA DRAWING







MATERIAL:

BODY & CONTACT & FERRULE:

BERYLLIUM COPPER

INSULATOR: PTFE

FINISH:

BODY, CONTACT & FERRULE:

GOLD OVER NICKEL

PERFORMANCE:

IMPEDANCE: 50 OHMS

DC TO 40.0 GHz. FREQ. RANGE:

MATERIAL:	SEE NOTES				
FINISH: SEE NOTES					
SURFACE AR	SURFACE AREA: N/A				
PROPRIETARY					
IS THE SOLE F ANY REPRODI WITHOUT THE	TION CONTAINED IN THIS DRAWIN PROPERTY OF SV MICROWAVE, IN JCTION IN PART OR AS A WHOLE WRITTEN PERMISSION OF /E, INC IS PROHIBITED.				

	DIMENSIONS ARE IN INCHES TOLERANCES:
	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' +15'
	DECIMAL: .X ±.030 .XX +.010
	.XXX ±.005
	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14 5M - 1994
	TERTIFICATION TOOT
;	THIRD ANGLE PROJECTION

1) ALL DIMENSIONS ARE IN 2) ALL DIMENSIONS ARE AF 3) BREAK CORNERS & EDG 4) CHAM. 15T & LAST THRE. 5) SURFACE ROUGHNESS 6 DIA.'S ON COMMON CENT WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	TER PLATING. ES .005 R. MAX. ADS. 3 _° MIL-STD-10.

UNLESS OTHERWISE SPECIFIED

4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNIESS 63-MIL-STD-10. 6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS			SMPM EF JACK FOR Ø.047 CABLE			
DRAWN:	BNK 04/07/22		I			
CHECKED:	SEE PDM	SIZE B	DWG. NO.	3221-4	0147	
APPROVED:	SEE PDM	S	CALE: 18:1		SHEET 1 OF	

MICROWAVE