

DURACELL Zinc Air Battery - 0% Mercury

Size: 675

DURACELL®		(-) ZA67
Nominal Voltage	1.45 V	
Rated Capacity	625 mAh at 620 ohm to 1.1 V @ 21°C and 50% RH	(+)
Typical Impedance (Fresh)	2.0 ohm @ 1kHz	⁹ 11.25 ¹⁰⁰
Typical Weight	1.68 g (0.059 oz)	
Volume	0.57 cm ³ (0.035 in ³)	
Terminals	Flat	
Operating Temperature Range	0°C to 50°C (32°F to 122°F)	
Recommended Storage Temperature	5°C to 30°C with 40-80% RH	
Shelf Life	4 years unactivated @ 21°C	
Designation	ANSI: 7003Z IEC: PR44	Dimensions shown are IEC / ANSI standard

Typical Discharge Characteristics at 21°C (70°F) and 50% RH





DURACEL BATTERIES

Berkshire Corporate Park Bethel, CT. 06801 U.S.A. Telephone: Toll-free 1-800-544-5454 www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

ZA6750217