

## AMPLIMITE

TE Internal #: 1534805-1 D-Sub Backshells & Clamps, Cover Kit, Single or Dual Cable Entry, 9 Position, Size 1, Shielded, Cable Exit Angle 45°, Wire & Cable View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: Cover Kit

Cable Clamp Type: Single or Dual Cable Entry

Number of Positions: 9

Compatible With Connector Shell Size: 1

Shielded: Yes

## Features

Product Type Features

Grommets	Without
Slide Latch	Without
D-Shaped Connector Accessories	Cover Kit
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	9
Body Features	
Shield Plating Material	None
Cable Clamp Material	Steel
Cable Clamp Type	Single or Dual Cable Entry
Cable Exit Angle	45°
Mechanical Attachment	
Screw & Hole Thread Size	14702
Dimensions	

**C** For support call+1 800 522 6752

09/16/2022 09:25AM | Page 1

## 1534805-1

D-Sub Backshells & Clamps, Cover Kit, Single or Dual Cable Entry, 9 Position, Size 1, Shielded, Cable Exit Angle 45°, Wire & Cable



Cable Insulation Diameter Range	4.8 – 9 mm[.189 – .354 in]
Operation/Application	
Compatible With Connector Shell Size	1
Shielded	Yes
Packaging Features	
Packaging Quantity	10
Packaging Method	Bag
Product Compliance For compliance documentation, visit the product page on TE.com>	
Product Compliance For compliance documentation, visit the product page on TE.com> EU RoHS Directive 2011/65/EU	Compliant
For compliance documentation, visit the product page on TE.com>	Compliant Compliant
For compliance documentation, visit the product page on TE.com> EU RoHS Directive 2011/65/EU	·
For compliance documentation, visit the product page on TE.com> EU RoHS Directive 2011/65/EU EU ELV Directive 2000/53/EC	Compliant

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# **Compatible Parts**

## 1534805-1

D-Sub Backshells & Clamps, Cover Kit, Single or Dual Cable Entry, 9 Position, Size 1, Shielded, Cable Exit Angle 45°, Wire & Cable





# Documents

Product Drawings HD20 COVER KIT 9POS WITH CABLE

English

CAD Files

3D PDF

English

**Customer View Model** 

ENG\_CVM\_1534805-1\_B1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_1534805-1\_B1.3d\_igs.zip

English

**Customer View Model** 

## ENG\_CVM\_1534805-1\_B1.3d\_stp.zip

## English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Application Specification

German

Product Environmental Compliance TE Material Declaration

English