Single Wall PTFE Heat Shrink Tubing



RoHS Compliant

Fluorinated Ethylene Propylene (FEP) Heat Shrink (HS)

Single wall heat shrink, provides the chemical and thermal characteristics of PTFE as well as the shrinking ability over inserted objects with exposure to moderate heat. Partial shrinkage occurs at 250°F with complete recovery at 450°F, with uses including soldered joints, parts, components, and fittings made of plastic, metal, or wood. During the shrink process on long objects, excess growth may cause wrinkles unless the tubing is allowed to slide forward over the object.

Specifications

Shrink Ratio : 1.67:1

Unrestricted Shrinkage Temperature : 1" and below: 410°F (210°C)

Over 1" Dla.: 430°F (221°C)

Maximum Service Temperature : -100°F to +400°F (-73°C to +200°C)

Colour : Translucent
Dielectric Strength : 1400 Volts/Mil

Dielectric Constant : 2.1 @ 100Hz ~ 60MHz

Applicable Specifications : AMS-DTL-23053/11; ASTM D 2902 Type II

Volume Resistivity : >10¹⁸ Ω .cm Tensile Strength : 2700 ~ 3500 PSI Elongation : 200% ~ 350%

Longitudinal Change : ±15%

Specific Gravity : 2.15 grams/cm³

Water Absorption : ≤0.01%

Flexibility : 3 (Material is rated on a scale of 1 ~ 10 for Flexibility;


1= Most Flexible and 10 = Most Rigid)

Flammability : UL94V-0 for resin

Good Abrasion Resistance

Excellent fungus, chemical, oil, solvent, and acids resistance

Diagram



Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Single Wall PTFE Heat Shrink Tubing



Dimensions				Dimensions					
Size		Recovered I.D. (Max) (Inches)	Recovered Wall Thickness (Inches)	2 Foot Lengths			6 Inch Lengths		
	Expanded I.D. (Min) (Inches)			Part Number	Pcs.	Total Foot- age (FT)	Part Number	Pcs.	Total Foot- age (FT)
3/32"	0.093	0.056	0.008 ±0.003	SST-006-2050-CLR	50	100	SST-006-6025-CLR	25	12.5
1/8"	0.125	0.075	0.01 ±0.003	SST-008-2050-CLR	50	100	SST-008-6025-CLR	25	12.5
3/16"	0.188	0.115	0.01 ±0.003	SST-012-2025-CLR	25	50	SST-012-6025-CLR	25	12.5
1/4"	0.25	0.15	0.01 ±0.003	SST-016-2025-CLR	25	50	SST-016-6025-CLR	25	12.5
3/8"	0.375	0.225	0.012 ±0.003	SST-024-2010-CLR	10	20	SST-024-6010-CLR	10	5
1/2"	0.5	0.3	0,015 ±0.004	SST-032-2010-CLR	10	20	SST-032-6010-CLR	10	5
3/4"	0.75	0.45	0.02 ±0.004	SST-048-2005-CLR	5	10	SST-048-6010-CLR	10	5
1"	1	0.6	0.025 ±0.005	SST-064-2005-CLR	5	10	SST-064-6010-CLR	10	5
1-1/2"	1.5	0.9	0.03 ±0.005	SST-096-2001-CLR	1	2	SST-096-6005-CLR	5	2.5
2"	2	1.2	0.03 ±0.005	SST-128-2001-CLR	1	2	SST-128-6005-CLR	5	2.5

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

