### **AK5** Series

Request Samples 🕥



5.0 x 3.2 x 1.3 mm RoHS/RoHS II Compliant MSL Level = 1

### Features

- 3rd overtone solution
- Ultra-Low jitter: 75 fs typ RMS (F= 156.25MHz LVPECL)
- Frequency range: 100MHz to 212.5MHz
- Lowest in-class power consumption (16mA typ LVDS)
- ± 20ppm & ± 25ppm stability (-40 to +85°C) options available (dependent on frequency)
- 3.3V, 2.5V, 1.8V Vdd supply
- LVPECL, LVDS, & HCSL differential output options
- Output enable standard

### Applications

- Networking and communications
- Gigabit Ethernet
- Fibre Channel
- SONET/SDH
- RF systems, base stations (BTS)
- Datacenter
- PCI Express
- Test & measurement

## Common Key Electrical Specifications

Parameters		Min.	Тур.	Max.	Units	Notes
Frequency Range		100		212.5	MHz	
Standard Available Frequencies			2.88MHz 125MHz Hz 200MHz 212			Contact Abracon for availability of frequencies not listed
Supply Voltage (Vdd) [Note 1]		2.97	3.3	3.63		Option "A"
		2.37	2.5	2.62	V	Option "B"
		1.71	1.8	1.89		Option "C"
	LVPECL		30	50		@ 200MHz; @ Vdd=3.3V
Supply Current (Idd)	LVDS		16	27	mA	@ 200MHz; @ Vdd=3.3V
	HCSL		17	30		@ 200MHz; @ Vdd=3.3V
Operating Temperature Range		-20		+70	°C	Option "D"
		-40		+85	C	Option "F" or "Q"
Storage Temperature		-55		+150	°C	
Frequency Accuracy (Initial Set- Tolerance) at time of shipment (Pre- Reflow) @ +25°C		-10	<±5	+10	ppm	Relative to carrier frequency
Frequency Stability over <sup>[Note 2, 3]</sup> Operating Temperature Range		-15		+15		Option "D" (-20°C to +70°C)
		-20		+20	ppm	Option "Q" (-40°C to +85°C)
		-25		+25		Option "F" (-40°C to +85°C)
Aging over 20 Year Product Life [Note 4]		-15		+15	ppm	



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

**AK5** Series

Request Samples 🕥

Check Inventory

(Pb)

**ESD** Sensitive

5.0 x 3.2 x 1.3 mm RoHS/RoHS II Compliant MSL Level = 1

### **Common Key Electrical Specifications Cont.**

Parameters			Min. Typ. Max. Units		Notes		
				- <i>J</i> <b>P</b> .		Chitis	
All-Inclusive Frequency Accuracy (Total			-40		+40	_	Option "D" (-20°C to +70°C)
Stability)			-45		+45	ppm	Option "Q" (-40°C to +85°C)
over 20 Year Product Life <sup>[Notes 4, 5]</sup>			-50		+50		Option "F" (-40°C to +85°C)
LVPECL			0.2	0.4		(a) Vdd=3.3V, $R_L$ =50 $\Omega$	
			0.3	0.6		(a) Vdd=2.5V, $R_L$ =50 $\Omega$	
				0.15	0.4		$ @ Vdd=3.3V, R_L=100\Omega $
Rise (Tr) / Fall (Tf) TimeLVDS20% to 80% Vpeak to peakHCSL		LVDS		0.15	0.4	ns	$@$ Vdd=2.5V, R <sub>L</sub> =100 $\Omega$
			0.3	0.5	115	@ Vdd=1.8V, $R_L$ =100 $\Omega$	
			0.3	0.5		@ Vdd=3.3V, $R_L$ =50 $\Omega$ to GND	
		HCSL		0.3	0.5		@ Vdd=2.5V, $R_L$ =50 $\Omega$ to GND
				0.3	0.6		@ Vdd=1.8V, $R_L$ =50 $\Omega$ to GND
Duty Cycle			45		55	%	
Start-up Time [Note 2]			< 2	5.0	ms		
Differential	LVPECL	V <sub>OH</sub>	Vdd-1.03		Vdd-0.88		RL=50 $\Omega$ to Vdd–2.0V on both
Output High	LVFECL	Vol	Vdd-1.85		Vdd-1.60		outputs
Voltage	e 1.000	V <sub>OH</sub>		1.40	1.60		RL=100Ω between
· · · ·	(V <sub>OH</sub> ) LVDS		0.90	1.10		V	both outputs
Output Low		V <sub>OH</sub>	0.40	0.74	0.85		RL=50 $\Omega$ to ground
Voltage (V <sub>OL</sub> )	-		-0.15	0.00	0.15		on each output
		•	0.595	0.750	0.930		LVPECL
Output Voltage Swing			0.250	0.350	0.450	V	LVDS
-	-	-	0.620	0.700	0.780		HCSL
		~ .	0.7*(V <sub>dd</sub> )			V	Output Enable or No Connect
Output Enab	le & Disable	Control			0.3*(V <sub>dd</sub> )		Output Disable (High Impedance)
Outpu	t Enable Tim	e		< 1	5.0	ms	
Output Disable Time					0.2	μs	
Output Disable Current Consumption				< 10	μA	$OE \le 0.3V$	
RMS Phase				115	140		@ Vdd=3.3V
Jitter <sup>[Note 6, 7, 8]</sup>		LVPECL		115	140	1	@ Vdd=2.5V
@ +25°C	<i>a</i> 200	200 LUDG		125	150		@ Vdd=3.3V
	MHz	LVDS		65	90	fsec	@ Vdd=2.5V
(12kHz-		HCCI		120	145	1	@ Vdd=3.3V
20MHz BW)		HCSL		125	150	-	@ Vdd=2.5V

Note 1: Supply voltage (Vdd) = 1.8V option not available with LVPECL output

Note 2: Relative to initial measured frequency @ +25°C

Note 3: Option Q only available in select frequencies. Please contact Abracon for availability

Note 4: Relative to post-reflow frequency

Note 5: Includes temperature stability, initial frequency accuracy, load pulling, power supply variation, and 20-year aging



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

**AK5** Series

Request Samples 🕥

Check Inventory 📎

(M)

ESD Sensitive

5.0 x 3.2 x 1.3 mm RoHS/RoHS II Compliant MSL Level = 1

**Common Key Electrical Specifications Cont.** 

	Parameters		Min.	Тур.	Max.	Units	Notes
					100		
	@ 156.25 MHz	LVPECL		75 80	100	-	@ Vdd=3.3V
				<u>80</u> 75	105 100	-	@ Vdd=2.5V
		LVDS				fsec	@ Vdd=3.3V
				100	125 145		@ Vdd=2.5V
		HCSL		120 120	145		@ Vdd=3.3V
				75	143		@ Vdd=2.5V
		LVPECL LVDS				_	@ Vdd=3.3V
				<u>80</u> 125	105 150	fsec	@ Vdd=2.5V @ Vdd=3.3V
	@ 148.5 MHz			123	130		
						_	@ Vdd=2.5V
		HCSL		115	140	_	@ Vdd=3.3V
				<u>115</u> 95	140 120		@ Vdd=2.5V
		LVPECL		125	120	_	@ Vdd=3.3V @ Vdd=2.5V
	@ 125 MHz @ 122.88 MHz					_	
		LVDS		185	210	fsec	@ Vdd=3.3V
RMS Phase Jitter				175	300		@ Vdd=2.5V
[Note 6, 7, 8] @ +25°C				145	170		@ Vdd=1.8V
		HCSL LVPECL		135	160		@ Vdd=3.3V
(101 11				125	150		@ Vdd=2.5V
(12kHz-				135	160		@ Vdd=1.8V
20MHz BW)				105	130		@ Vdd=3.3V
				115	140		@ Vdd=2.5V
		LVDS		195	220		@ Vdd=3.3V
				180	205		@ Vdd=2.5V
				145	170		@ Vdd=1.8V
		HCSL		125	150		@ Vdd=3.3V
				115	140		@ Vdd=2.5V
				180	205		@ Vdd=1.8V
	@ 100 MHz	LVPECL		185	210	-	@ Vdd=3.3V
				160	185		@ Vdd=2.5V
		LVDS		305	330		@ Vdd=3.3V
				300	325	fsec	@ Vdd=2.5V
				195	220		@ Vdd=1.8V
		HCSL		170	195		@ Vdd=3.3V
				180	205		@ Vdd=2.5V
				175	200		@ Vdd=1.8V

Note 6: Guaranteed by characterization; RMS Phase Jitter specifications are inclusive of any spurs


Note 7: Phase jitter measured with Keysight E5052B Signal Source Analyzer

Note 8: Refer to the next section for phase noise test setup and representative phase noise plots



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 




ABRACON

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

ISO9001-2015 CERTIFIED



ABRACON


5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

**AK5** Series Request Samples Check Inventory 5.0 x 3.2 x 1.3 mm  $(\mathcal{D})$  $(\Sigma)$ **RoHS/RoHS II Compliant ESD** Sensitive (Pb) MSL Level = 1


Recommended Test Circuit [Note 11]

# LVPECL



Vdd= 3.3V: R1=R3=127Ω; R2=R4=82.5Ω Vdd= 2.5V: R1=R3=250Ω; R2=R4=62.5Ω






Note 11: Recommended test circuit images are representative of when the OE Function is located on Pin 1; when the OE Function is located on Pin 2, then Pin 1=No Connect & Pin 2=OE or No Connect.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

ABRACON IS ISO9001-2015 CERTIFIED



LVDS




Request Samples




5.0 x 3.2 x 1.3 mm RoHS/RoHS II Compliant MSL Level = 1

**Typical Frequency vs. Temperature Characteristics** 



### **Differential Output Wave from**



**AK5 Series** 


Request Samples 🜔

Check Inventory Sensitive

5.0 x 3.2 x 1.3 mm RoHS/RoHS II Compliant MSL Level = 1


Phase Noise Test Setup [Note 9]

- Keysight E5052B Signal Source Analyzer
- Integration Bandwidth = 12kHz to 20MHz
- Spurious Activity (entire plot trace) = Not omitted (Normalized in dBc/Hz)
- Specifed Spur Omission Function = Not enabled
- IF Gain = 20dB
- Correlation = 5
- Average = 3



#### F=156.2500MHz | V<sub>dd</sub>=3.3V | LVDS RMS Phase Jitter = 75 fsec






Note 9: Contact Abracon for phase noise plots at alternative supply voltage (V<sub>dd</sub>) & differential output formats



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 




Note 9: Contact Abracon for phase noise plots at alternative supply voltage (V<sub>dd</sub>) & differential output formats



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 




F=100.0000MHz | V<sub>dd</sub>=1.8V | HCSL RMS Phase Jitter = 176 fsec

150.0

160.0

Start 10 H



Note 9: Contact Abracon for phase noise plots at alternative supply voltage (V<sub>dd</sub>) & differential output formats



450.1

160.0

-170.0

Start 10 H


5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 

w 2.5V A



### Recommended Reflow Profile [Note 12]




Zone	Description	Temperature	Time		
1	Preheat / Soak	$\begin{array}{l} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{array}$	60 ~ 180 sec.		
2	Reflow	T <sub>L</sub> 217°C	60 ~ 150 sec.		
3	Peak heat	$T_P$ 260°C±5°C	$20 \sim 40$ sec.		

Note 12: Can withstand 2 reflows Note 13: Ramp Up Rate  $(T_L \rightarrow T_P) = 3^{\circ}C / \text{sec. MAX}$ Note 14: Ramp Down Rate  $(T_P \rightarrow T_L) = 6^{\circ}C / \text{sec. MAX}$ Note 15: Time 25°C to Peak Temperature  $(25^{\circ}C \rightarrow T_P) = 8$  minutes MAX All temperatures refer to topside of the package, measured on the package body surface



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22** 



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 10-06-22**