

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300100490

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 4.0m (13.12') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Industrial Cordsets

Series

130010

Connector End A

Mini-Change

Connector End B

Mini-Change

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Mini-Change Connectors

Product Name

Mini-Change

Protocol

DeviceNet

Region

America

Taxonomy

Circular Industrial Cordsets

Type

Double Ended

UPC

78678884065

Physical

Cable Diameter

10.41mm (.410")

Cable Length

4.0m (13.12')

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

TPE

Material - Connector Body

TPE

Material - Coupling Nut

Black Epoxy Coated Zinc

Material - Plating Mating

Gold

Net Weight

682.567/g

Orientation

Straight to Straight

Poles

3

Temperature Range - Operating

-20° to +105°C

Wire Size AWG

16

Wire/Cable Type

TC-ER

Electrical

Current - Maximum per Contact

13.0A

Voltage - Maximum

600V

Material Info

Engineering Number

113030K13M040

Reference - Drawing Numbers

Sales Drawing

SD-130010-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000406200_00_000.pdf

CER_4000410292_00_000.pdf

Search Parts in this Series

130010 Series

This document was generated on 09/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION