




REVISIONS			
REV	DESCRIPTION, EGN, EAR NO.	DATE	APP'D
A	PROPOSAL DRAWING	MAY 09/16	L.CHAN
B	PROPOSAL DRAWING	OCT17/19	L.CHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

LOCATE HOLES
 $\text{⌀} \text{⌀} .005 [0.13]$
 POSITION DIMENSIONS
 ARE BASIC



MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0,
 COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE
 PLATING: 50 u" [1.27 MICRONS] MIN.
 GOLD PLATED ON MATING SURFACES.
 50 u" [1.27 MICRONS]
 MIN. NICKEL UNDERPLATE
 100 u" [2.54 MICRONS]
 MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH TIN DIPPED ON SOLDER TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
 WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM
 FOR 5 SEC MAXIMUM.

ENVIRONMENTAL: OPERATING TEMPERATURE: -55°C to 85°C

AMPHENOL PART NUMBER: RJHSE-7440

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN	W.QIU	MAY.09/16	Amphenol Canada Corp. Commercial Products
PRIMARY UNITS INCH	CHECKED	L.CHAN	MAY.09/16	
SECONDARY UNITS MILLIMETER	M.E. APP'D			
REFERENCE IN PARENTHESES	Q.A. APP'D			
1 DECIMAL PLACE ±0.025	DWG APP'D			HIGH SPEED MODULAR JACK, 6 POS., 4 STAMPED CONTACTS, SHIELD WITH SIDE GROUND TABS, -RoHS COMPLIANT
2 DECIMAL PLACE ±0.020	ENG. REL. NO.			
3 DECIMAL PLACE ±0.015	REF.			DWG NO. P-RJHSE-7440
ANGULAR DEGREES ±1°	THIRD ANGLE PROJECTION			REV B
	DO NOT SCALE DRAWING			CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1