




LOC		DIST		REVISIONS			
FT	13	P	LTR	DESCRIPTION	DATE	DMN	APVD
		0		RLSE PER NPR 5498 WAS 95-5019-8	21 MAR 96	-	-
		A		ADDED -1, -3 PER EC 0320-73-97	21 MAR 97	CO	AF
		B		REV PER EC 0320-399-97	22 JAN 98	MB	RW

- 1 WIRE SIZE AND AMP LOGO APPEAR ON OUTSIDE OF WIRE BARREL.
- 2 SOCKET CONTACT: 0.38µm [0.00015] MIN GOLD PER MIL-G-45204 ON CONTACT MATING END, GOLD FLASH ON REMAINDER, ALL OVER 1.27µm [0.00050] MIN NICKEL PER QQ-N-390.
 CONTACT STRIP: 0.76µm [0.00030] MIN GOLD PER MIL-G-45204 OVER 1.02µm [0.00040] MIN NICKEL PER QQ-N-390.
 RETENTION CLIP: 2.54µm [0.00100] MIN NICKEL PER QQ-N-290.
- 3 RETENTION CLIP: PHOSPHOR BRONZE PER QQ-B-750.
 SOCKET CONTACT: COPPER PER QQ-C-576.
 CONTACT STRIP: BERYLLIUM COPPER PER QQ-C-533.
- 4 SOCKET CONTACT: 1.27µm [0.00050] MIN SILVER PER QQ-S-365, ALL OVER 1.27µm [0.00050] MIN NICKEL PER QQ-N-290.
 CONTACT STRIP: 5.08µm [0.00200] MIN SILVER PER QQ-S-365, ALL OVER 1.02 µm [0.00040] MIN NICKEL PER QQ-N-290.
 RETENTION CLIP: 2.54µm [0.00100] MIN NICKEL PER QQ-N-290.



2	DETAIL X	213843-4
4	DETAIL X	213843-3
2	-	213843-2
4	-	213843-1
FINISH	LOOSE PIECE	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		FINISH:	
0 PLC	±	0 PLC	±	SEE TABLE	
1 PLC	±	1 PLC	±		
2 PLC	±	2 PLC	±		
3 PLC	±	3 PLC	±		
4 PLC	±	4 PLC	±		
ANGLES	±	ANGLES	±		

DMN	C. OBERMAN	21 MAR 96	AMP AMP Incorporated Harrisburg, PA 17105-3608
CHK	R. STONE	25 MAR 96	
APVD	G. STEINHAUER	26 MAR 96	
NAME	SOCKET CONTACT ASSEMBLY, 8-10 AWG, POWERBAND, METRIMATE		
SIZE	A1	00779	DRAWING NO
WEIGHT	-	-	SCALE
CUSTOMER DRAWING	SCALE 10:1		SHEET 1 OF 1