

Innovative Service Around the Globe

DATA SHEET POSITIVE TEMPERATURE COEFFICIENT AC/DC POWER SUPPLY SMD0603 series

RoHS compliant & Halogen free



AGEO Circuit Protection

POSITIVE TEMPERATURE COEFFICIENT SMD0603

Positive Temperature Coefficient (PTC) Data Sheet

Description

The 0603 series provides miniature surface mount resettable overcurrent protection with holding current from 40mA to 500mA. This series is suitable for ultra portable applications where space is at a premium and the device current is low.

Features

- RoHS compliant and lead-free
- Fast response to fault current
- Halogen-free
- UL/CULE482628
- RoHS2011/65/EU

Applications

Oct. 06. 2020 V.I

- USB hubs, ports and peripherals
- Set-top-box and HDMI
- Game console port protection

Part Number Code and Marking

- Low profile
- Compatible with high temperature solders
- Compact design saves board space
- TUV B160696048001
- Halogen FreeEN 14582:2007
- Motherboard USB & IEEE 1394 protection
- Optical disk drives
- General electronics

SMD 0603 B TFT/ Special Voltage Rating (Optional) Thickness Version (Optional) Lead-Free Holding Current Rating Delimiter Device Dimensions: Length/Width (Unit: 1/100 inch) Surface Mount Device

Part Number	Marking	Part Number	Marking
SMD0603B004TF	—	SMD0603B025TF	I
SMD0603B010TF	С	SMD0603B035TF	F
SMD0603B020TF	Н	SMD0603B050TF	J



2

9


YAGEO Circuit Protection

POSITIVE TEMPERATURE COEFFICIENT SMD0603

Product Specification


<u>3</u> 9

Dimensions and PAD-SIZE



Part	ŀ	٩	E	3	(C	[)	E	E
Number	Min.	Max.								
SMD0603B004TF	1.40	1.80	0.60	1.00	0.40	1.00	0.15	0.50	-	0.40
SMD0603B010TF	1.40	1.80	0.60	1.00	0.40	1.00	0.15	0.50	-	0.40
SMD0603B020TF	1.40	1.80	0.60	1.00	0.40	1.00	0.15	0.50	-	0.40
SMD0603B025TF	1.40	1.80	0.60	1.00	0.40	1.00	0.15	0.50	-	0.40
SMD0603B035TF	1.40	1.80	0.60	1.00	0.55	1.55	0.15	0.50	-	0.40
SMD0603B050TF	1.40	1.80	0.60	1.00	0.55	1.55	0.15	0.50	-	0.40

Recommended Pad Layout (mm)





POSITIVE TEMPERATURE COEFFICIENT SMD0603

4

Electrical Characteristics

Part	I _{hold}	I _{trip}	V _{max}	I _{max} P _{d typ.}		I _{max}	I _{max}	I _{max}		imum To Trip	Resis	tance
Number	(A)	(A)	(Vdc)	(A)	(W)	Time (Sec.)	Current (A)	R _{min} (Ω)	R _{1max} (Ω)			
SMD0603B004TF	0.04	0.12	24	20	0.5	1.00	0.20	4.00	40.0			
SMD0603B010TF	0.10	0.30	15	40	0.5	1.00	0.50	0.90	6.0			
SMD0603B020TF	0.20	0.50	9	40	0.5	0.60	1.00	0.55	3.5			
SMD0603B025TF	0.25	0.55	9	40	0.5	0.08	8.00	0.50	3.0			
SMD0603B035TF	0.35	0.75	6	40	0.5	0.10	8.00	0.20	1.0			
SMD0603B050TF	0.50	1.00	6	40	0.5	0.10	8.00	0.10	0.68			

Note on Electrical Characteristics

- Vocabulary
- I_{hold} = Hold current: maximum current device will pass without tripping in 23 °C still air.
- + I_{trip} = Trip current: minimum current at which the device will trip in 23 $^\circ\!\!\mathbb{C}$ still air.
- V_{max} = Maximum voltage device can withstand without damage at rated current (I_{max})
- I_{max} = Maximum fault current device can withstand without damage at rated voltage (V_{max})
- + $P_{d \; typ.}$ = Typical power dissipated from device when in the tripped state at 23 $^\circ\!\mathrm{C}$ still air.
- R_{min} = Minimum resistance of device in initial (un-soldered) state.
- R_{1max} = Maximum resistance of device at 23 °C measured one hour after tripping or reflow soldering of 260 °C for 20 sec.
- Value specified is determined by using the PWB with 0.090"*1.5oz copper traces.
- Caution: Operation beyond the specified rating may result in damage and possible arcing and flame.

Circuit Protection

> **IVE TEMPERATURE COEFFICIENT** SMD0603

Polymeric PTC Selecting Guide

- Determine the following operating parameters for the circuits:
 - Normal operating current (Ihold)
 - Maximum circuit voltage (V_{max})
- Normal operating temperature surrounding device (min°C/max°C) Select the device from factor and dimension suitable for the application
- Compare the maximum rating for V_{max} and I_{max} of the PPTC device with the circuit in application and make sure the circuit's requirement does not exceed the device rating.

Maximum interrupt current (I_{max})

- Check that PPTC device's trip time (time-to-trip) will protect the circuit.
- Verify that the circuit operating temperature is within the PPTC device's normal operating temperature range.
- Verify that performance and suitability of the chosen PPTC device in the application.

WARNING

Mechanical Stress

- PPTC devices will undergo a thermal expansion during fault condition. If PPTC devices are installed or placed in an application where the space between PPTC devices and the surrounding materials (e.g., covering materials, packaging materials, encapsulate materials and the like) is insufficient, it will cause an inhibiting effect upon the thermal expansion. Pressing, twisting, bending and other kinds of mechanical stress will also adversely affect the performance of the PPTC devices, and shall not be used or applied.
- Chemical Pollutants
 - Silicone-based oils, oils, solvents, gels, electrolytes, fuels, acids, and the like will adversely affect the properties of PPTC devices, and shall not be used or applied.
- Electronic and Thermal Effect
 - PPTC devices are secondary protection devices and are used solely for sporadic, accidental over-current or over-temperature error condition, and shall NOT be used if or when constant or repeated fault conditions (such fault conditions may be caused by, among others, incorrect pin-connection of a connector) or over-extensive trip events may occur.
 - PPTC devices are different from fuses and, when a fault condition occurs, will go into high-resistance state and do not open circuit, in which case the voltage at such PPTC devices may reach a hazardous level.
 - · Operation over the maximum rating or other forms of improper use may cause failure, arcing, flame and/or other damage to the PPTC devices.
 - Conductive material contamination, such as metal particle, may induce shortage, flame or arcing.
 - Due to the inductance, the operation circuits may generate a circuit voltage (Ldi/dt) above the rated voltage of PPTC devices. which shall not be used under such circumstances.
- General
 - Customers shall evaluate and test the properties of PPTC devices independently to verify and ensure that their individual applications will be met.
 - The performance of PPTC devices will be adversely affected if they are improperly used under electronic, thermal and/or mechanical procedures and/or conditions non-conformant to those recommended by manufacturer.
 - Customers shall be responsible for determining whether it is necessary to have back-up, failsafe and/or fool-proof protection To avoid or minimize damage that may result from extra-ordinary, irregular function or failure of PPTC devices.
 - Any and all responsibilities and liabilities are disclaimed if any item under this notice of warning is not complied with.


YAGEO Circuit Protection

POSITIVE TEMPERATURE COEFFICIENT SMD0603

6

9


Thermal Derating Curve



Thermal Derating Chart

Part		Ambient Operation Temperature							
Number	-40 ℃	-20 ℃	0 ℃	23 ℃	40 ℃	50 ℃	60 ℃	70 ℃	85 ℃
SMD0603B004TF	0.052	0.048	0.044	0.040	0.032	0.028	0.024	0.020	0.012
SMD0603B010TF	0.130	0.120	0.110	0.100	0.080	0.070	0.060	0.050	0.030
SMD0603B020TF	0.270	0.250	0.230	0.200	0.170	0.140	0.120	0.100	0.070
SMD0603B025TF	0.320	0.290	0.270	0.250	0.210	0.180	0.160	0.140	0.100
SMD0603B035TF	0.470	0.410	0.380	0.350	0.290	0.260	0.240	0.200	0.140
SMD0603B050TF	0.670	0.590	0.540	0.500	0.410	0.370	0.340	0.290	0.200


Average Time-Current Curve



A-SMD0603B004TF B-SMD0603B010TF C-SMD0603B020TF D-SMD0603B025TF E-SMD0603B035TF F-SMD0603B050TF



Soldering Parameters



260℃

20-40 seconds

6℃/second max.

8 minutes max.

0°C~35°C, ≤70%RH

Recommended reflow methods: I	R. vapor phase oven.	. hot air oven. N₂	environment for lead-free

• Recommended maximum paste thickness is 0.25mm (0.010 inch)

Peak Temperature (T_P)

Time 25℃ to Peak Temperature

Ramp-down Rate

Storage Condition

• Device can be cleaned using standard industry methods and solvents.

Time within 5 $^{\circ}$ C of actual Peak Temperature (t_P)

Note 1: All temperature refer to topside of the package, measured on the package body surface.

Note 2: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.



YAGEO | Circuit Protection

POSITIVE TEMPERATURE COEFFICIENT

SMD0603

Environmental Specifications

Operating / Storage temperature	-40°℃ to +85°℃
Maximum Device Surface Temperature in Tripped State	125℃
Passive Aging	+85℃, 1000 hours ±50% typical resistance change
Humidity Aging	+85℃, 85%RH, 1000 hours ±50% typical resistance change
Thermal Shock	MIL-STD-202, Method 107G +85℃/-40℃ 20 times -50% typical resistance change
Solvent Resistance	MIL-STD-202, Method 215 No change
Vibration	MIL-STD-883C, Method 2007.1, Condition A No change
Moisture Level Sensitivity	Level 1, J-STD-020C

Physical Specifications

Terminal Material	Solder-Plated Copper (Solder Material: Matte Tin (Sn))
Terminal Solderability	Meets EIA Specification RS186-9E, ANSI/J-STD-002 Category 3.

YAGEO | Circuit Protection

POSITIVE TEMPERATURE COEFFICIENT SMD0603

9

Packaging

Part Number	Part Number	Part Number	Quantity
SMD0603B004TF	4000	SMD0603B025TF	4000
SMD0603B010TF	4000	SMD0603B035TF	4000
SMD0603B020TF	4000	SMD0603B050TF	4000

© 8mm tape on 7 inch reel per EIA-481 (equivalent to IEC286, part 3)

