




8133-8165

Precision Diagonal Cutters with Tapered Head



PRODUCT DETAILS

- 80 series precision diagonal cutters with tapered head
- ESD safe mono-material handles with return spring
- Micro-bevel, flush & ultra-flush cut
- The stated cutting capacity is for copper wire
- Suitable for cutting copper
- High performance alloy steel
- Burnished finish
- Numerically controlled machine grinding ensures edge angle accuracy and contact, increasing tool reliability and consistency
- Precision induction hardened edges 63-65 HRC
- Screw joint minimises friction and maximises alignment of cutting edges
- Ideal for assembly work where accessibility is a consideration
- CO standard handle shape in conductive material



C	0.50 in	D	6 mm	D	0,24 inch
F	1,2 mm	F	0,05 in	g	49 g
Ω	Dissipative				

C	0.50 in	D	6 mm	D	inch
F	1,2 mm	F	0,05 in	g	49 g
Ω	Dissipative				

Product: 8155

	Tapered		M		Ultra-Flush®
	0.2-1.25 mm		0.01-0.05 in		
		A	112.5 mm	A	4.43 in
B	13 mm	B	0,51 in	C	12,5 mm
C	0.50 in	D	6 mm	D	0,24 inch
F	1,2 mm	F	0,05 in	g	49 g
Ω	Dissipative				

Product: 8163

	Tapered		L		Micro-Bevel®
	0.4-2.0 mm		0.02-0.08 in		0.3-0.6 mm
	0.01-0.02 in	A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in	g	88 g
Ω	Dissipative				

Product: 8164

	Tapered		L		Flush
	0.3-2.0 mm		0.01-0.08 in		0.3-0.6 mm
	0.01-0.02 in	A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in	g	88 g
Ω	Dissipative				

Product: 8165

	Tapered		L		Ultra-Flush®
	0.3-1.6 mm		0.01-0.06 in		
		A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in	g	88 g
Ω	Dissipative				

Product: 8144 CO

	Tapered		S		Flush
	0.2-1.25 mm		0.01-0.05 in		
		A	110 mm	A	4.33 in
B	10,5 mm	B	0,41 in	C	10 mm
C	0.39 in	D	6 mm	D	0,24 inch
F	0,8 mm	F	0,03 in	g	46 g
Ω	Conductive				

Product: 8154 CO

	Tapered		M		Flush
	0.2-1.6 mm		0.01-0.06 in		
		A	112.5 mm	A	4.43 in
B	13 mm	B	0,51 in	C	12,5 mm
C	0.50 in	D	6 mm	D	0,24 inch
F	1,2 mm	F	0,05 in	g	49 g
Ω	Conductive				

Product: 8163 CO

	Tapered		L		Micro-Bevel®
	0.4-2.0 mm		0.02-0.08 in		
		A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in	g	88 g
Ω	Conductive				

Product: 8165 CO

	Tapered		L		Ultra-Flush®
	0.3-1.6 mm		0.01-0.06 in		
		A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in	g	88 g
Ω	Conductive				