

AMEL40-277HAVZ

Click to
ORDER
samples



Encapsulated

The AMEL40-277HAVZ series is an efficient 40W AC-DC power supply module. Offering a commercial wide input voltage range of 85-305VAC, output voltage ranges from 3.3-48V, low power consumption, high efficiency, high reliability and safer isolation.

This new series offers great operating temperatures, from -40°C to 85°C with full power up to 50°C and features an isolation of 4200VAC with OVCI rating for improved reliability and system safety. Additionally, it has 2000m-5000m operational altitude de rating Furthermore, a high MTBF of 500,000h, output short circuit protection (OSCP), output over-current protection (OCP) and an output over-voltage protection (OVP) come standard with the series.

The AMEL40-277HAVZ is great for grid power, industrial instrumentation and controls, communication, and civil applications.

Features

- Universal Input: 85 - 305VAC/100 - 430VDC
- Operating Temp: -40 °C to +85 °C
- High isolation voltage: 4200VAC
- Low ripple & noise, 150mV(p-p) max.
- Output short circuit, over-current, over-voltage protection
- Low no-load power consumption of 0.3W
- Efficiency up to 90%
- OVC III(EN62477, 5000m altitude)
- Designed to meet : IEC/UL/EN62368-1, CISPR32/EN55032, EN/UL62368, EN61000-4, EN61558, IEC/EN60335/62477



Training



Product Training Video
(coming soon)




Press Release

Coming Soon!

Application Notes

Summary

AMEL40-277HAVZ



Applications



Power Grid



Industrial



Telecom

Models & Specifications

Single Output

Model	Input Voltage (VAC/Hz)	Input Voltage (VDC)	Max Output wattage (W)	Output Voltage (V)	Output Current max (A)	Maximum capacitive load (μF)	Efficiency @ 230VAC Typ. (%)
AMEL40-5S277HAVZ	85-305/47-440	100-430	35	5	7	6600	86
AMEL40-12S277HAVZ	85-305/47-440	100-430	40	12	3.33	4400	89
AMEL40-15S277HAVZ	85-305/47-440	100-430	40	15	2.67	3000	90
AMEL40-24S277HAVZ	85-305/47-440	100-430	40	24	1.67	1500	89
AMEL40-48S277HAVZ	85-305/47-440	100-430	40	48	0.83	470	90

Input Specifications

Parameters	Conditions	Typical	Minimum	Maximum	Units
Input current	115VAC			1	A
	230VAC			0.6	A
Inrush current	115VAC	30			A
	230VAC	60			A
Leakage	277VAC, 50Hz			0.1	mA RMS
Input Frequency			47	63	Hz
Input Voltage Range	AC Input		85	305	VAC
	DC Input		100	430	VDC
Hot Plug		Unavailable			
Recommended External I/p Fuse		3.15A/300V, Slow blow, required			

Output Specifications

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy		±2		%
Line regulation	Full load	±0.5		%
Load Regulation	5V output	±2		
	Others	±1		
Ripple & Noise*	20MHz bandwidth (peak to peak value)	100	150	mV p-p
Hold up time	115VAC	8		ms
	230VAC	50		ms

* Ripple and Noise are measured at 20MHz bandwidth with a 10μF electrolytic capacitor and a 1μF ceramic capacitor. Please refer to the application note for specific details. Note: *The "parallel cable" method is used for ripple and noise test, output parallel 10uF electrolytic capacitor and 1uF ceramic capacitor, please refer to AC-DC Converter Application Notes for specific information;

Isolation Specification				
Parameters	Conditions	Typical	Maximum	Units
Tested I/O voltage	60 sec, leakage $\leq$ 5mA	4200		VAC
Resistance	500VDC	>100		MΩ

General Specifications					
Parameters	Conditions	Typical	Minimum	Maximum	Units
Protection class		Class II			
Overvoltage category		OVC III			
Over current protection	Auto recovery	≥ 130			% of Iout
Over voltage protection	5Vout, voltage clamp, hiccup			6.3	VDC
	12Vout, voltage clamp, hiccup			16	VDC
	15Vout, voltage clamp, hiccup			25	VDC
	24Vout, voltage clamp, hiccup			35	VDC
	48Vout, voltage clamp, hiccup			60	VDC
Short circuit protection		Hiccup, Continuous, Auto recovery			
Operating temperature	See derating graph	-40 to +85			°C
Storage temperature		-40 to +85			°C
Wave soldering temperature	Duration 5 - 10s	260 ± 5			°C
Manual soldering temperature	Duration 3 - 5s	360 ± 10			°C
No-load power consumption	230VAC	0.3		0.55	W
Power Derating	-40 °C to -25 °C, 85VAC to 200VAC Input		4		%/°C
	+50 °C to +70 °C		2.5		%/°C
	+70 °C to +85 °C		1.67		%/°C
	85VAC to 100VAC		1.33		%/VAC
	277VAC to 305VAC		0.71		%/VAC
	2000 - 5000m		6.67		%/km
Temperature coefficient		±0.02			%/°C
Cooling		Free air convection			
Humidity	Non-condensing			95	% RH
Case material		Black Plastic (flammability to UL 94V-0)			
Weight	PCB mountable models	100			g
Dimensions (L x W x H)	PCB mountable models		2.74 x 1.54 x 0.95 inches (69.50 x 39.00 x 24.00 mm)		
MTBF		> 500,000 hrs (MIL-HDBK - 217F, t=+25°C)			
	NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.				


Safety Specifications

Parameters


Agency approvals	Designed to meet IEC/UL/EN62368-1, IEC/EN60335-1/62477-1, EN61558-1	
Standards	EMC - Conducted and radiated emission	CISPR32 / EN55032, class B
	Electrostatic Discharge Immunity	IEC/EN 61000-4-2 Contact $\pm 6\text{KV}$, Air $\pm 8\text{KV}$, Criteria A
	RF, Electromagnetic Field Immunity	IEC/EN 61000-4-3 10V/m, Criteria A
	Electrical Fast Transient/Burst Immunity	IEC/EN 61000-4-4 $\pm 2\text{KV}$, Criteria A
	Surge Immunity	IEC/EN 61000-4-5 L-L $\pm 2\text{KV}$, Criteria A IEC/EN 61000-4-5 L-L $\pm 2\text{KV}$, L-GND $\pm 4\text{KV}$, Criteria A with the recommended EMC circuit
	RF, Conducted Disturbance Immunity	IEC/EN 61000-4-6 10Vr.m.s, Criteria A
	Voltage dips, Short Interruptions Immunity	IEC/EN 61000-4-11 0%, 70%, Criteria B

Derating


Thermal Derating for all output models Free Air Convection



Input Derating




Altitude Derating for all models




Efficiency Curves




Efficiency vs Output Load



Efficiency vs Input Voltage(Full Load)



Typical Application Circuit




Model	C1	C2	TVS
5Vout	1 μ F/50V	330 μ F/16V	7V
12Vout		330 μ F/16V	20V
15Vout		220 μ F/25V	20V
24Vout		100 μ F/30V	30V
48Vout		47 μ F/63V	64V



For filtering components:

The C2 capacitor is recommended to use electrolytic type with high frequency and low ESR rating. The C1 capacitor is recommended to use ceramic type for filtering high-frequency noise.

Recommended EMC Circuit



Dimensions



Dimensions mm (inch).
Pin diameter tolerance ± 0.1 (± 0.004)
General tolerance ± 0.5 (± 0.02)

Pin Output Specifications	
Pin	Function
1	AC Input (L)
2	AC Input (N)
3	-V Output
4	+V Output

NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.