



Lithium Coin Cell - CR 1620

- Reliable energy for your application
- Standard cells and customized packs
- ESD protection
- UL recognized
- Battery Certification Experts



RoHS compliant



Pb free



REACH compliant



Conflict mineral free


Technical Data Sheet · CR 1620

SPECIFICATIONS


Nominal Voltage	3V
Jauch part number	245989
Nominal Capacity	75 mAh
Standard Load	47 kΩ
Standard Current	0.065 mA
Max. Continuous Current	0.65 mA
Max. Pulse Current	8 mA
Operating Temperature	-30°C to +70°C*
Weight	Approx. 1.25 gr.
Chemistry	Li/MnO ₂
UL1642	MH62838

* In applications where the battery is exposed to temperatures >60°C, please contact Jauch.


DIMENSIONS (mm)




DISCHARGE CHARACTERISTICS




TEMPERATURE CHARACTERISTICS



PULSE DISCHARGE CHARACTERISTICS



LOAD VS: CAPACITY



Wide assortment of mounting options, including through hole, surface mount and wire terminals.

Contact Jauch for more information
batterytechnology@jauch.com