

# TECHNICAL DATA SHEET


**PRO-SIGNAL**

RoHS  
Compliant

## 5mm Diffused Red and Green / Yellow Bi-Colour Common Cathode LEDs

Part No.	Pack Size	Diffused Colour	Wavelength at IF = 20mA	Forward Voltage (VF) at IF = 20mA	DC Forward Current	Reverse Current at VR = 5V
PSG91922	5	Red and Green / Yellow	R: 620 – 625	1.8V to 2.4V	15mA to 18mA	≤10
PSG91923	50		YG: 570 - 572			

Part No.	Pack Size	Luminous Intensity at IF = 20mA	Maximum Power dissipation	Peak Forward Current (IFM)	Reverse Voltage
PSG91922	5	R: 600 – 800mcd	PM = 80mW	30mA	5V
PSG91923	50	G: 200 – 300mcd			



**Important Notice:** This data sheet and its contents (the "Information") belong to pro-SIGNAL. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-SIGNAL assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-SIGNAL was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-SIGNAL's liability for death or personal injury resulting from its negligence.

**PRO-SIGNAL**