


High Power Aluminum Nitride, Wraparound Surface Mount, Precision Thin Film Chip Resistor (Up to 6 W)



LINKS TO ADDITIONAL RESOURCES



PCAN series chip resistors are designed on aluminum nitride ceramic substrates with enlarged backside terminations to reduce the thermal resistance between the topside resistor layer and the solder joint on the end users circuit assembly.

Actual power handling capability is limited by the end user mounting process. As with any high power chip resistor the ability to remove the heat is critical to the overall performance of the device.

FEATURES

- High thermal conductivity aluminum nitride substrate
- Power rating up to 6.0 W
- Resistance range 2 Ω to 30.1 kΩ
- Resistor tolerance to ± 0.1 %
- TCR to ± 25 ppm/°C
- Flame resistant UL 94 V-0
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available

HALOGEN
FREE

GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

APPLICATIONS

- Power supplies
- Power switching
- Braking system

TYPICAL PERFORMANCE

| | ABSOLUTE |
|------|----------|
| TCR | 25 |
| TOL. | 0.1 |

STANDARD ELECTRICAL SPECIFICATIONS

| TEST | SPECIFICATIONS | CONDITIONS |
|--------------------------------|---|-------------------|
| Material | Passivated nichrome | - |
| Resistance Range | 2 Ω to 30.1 kΩ | - |
| TCR: Absolute | 25 ppm/°C (standard) and 100 ppm/°C | - |
| Tolerance: Absolute | 0.1 %, 0.25 %, 0.5 %, 1.0 %, 2.0 %, and 5.0 % | -55 °C to +150 °C |
| Power Rating: Resistor | 0.5 W to 6.0 W ⁽¹⁾ | Maximum at +70 °C |
| Stability: Absolute | ΔR 1.0 % | 1000 h at +70 °C |
| Voltage Coefficient | < 0.1 ppm/V | - |
| Working Voltage | 75 V to 100 V | - |
| Operating Temperature Range | -55 °C to +155 °C | - |
| Storage Temperature Range | -55 °C to +155 °C | - |
| Noise | < -30 dB | - |
| Shelf Life Stability: Absolute | ± 0.01 % | 1 year at +25 °C |

Note

⁽¹⁾ Dependant on component mounting by user

COMPONENT RATINGS

| CASE SIZE | POWER RATING (mW) | WORKING VOLTAGE (V) | RESISTANCE RANGE (Ω) |
|-----------|---------------------|---------------------|----------------------|
| 0603 | 500 ⁽¹⁾ | 75 | 2 to 30.1K |
| 0805 | 1000 ⁽¹⁾ | 100 | 2 to 30.1K |
| 1206 | 2000 ⁽¹⁾ | 100 | 2 to 30.1K |
| 2512 | 6000 ⁽¹⁾ | 100 | 2 to 30.1K |

Note

⁽¹⁾ Dependant on component mounting by user

| ENVIRONMENTAL TESTS | | |
|---|-------------|----------------------------|
| ENVIRONMENTAL TEST ⁽¹⁾ | TEST LIMITS | TYPICAL VISHAY PERFORMANCE |
| Resistance temperature characteristic | ± 25 ppm/°C | ± 15 ppm/°C |
| Maximum ambient temperature at rated wattage | +70 °C | +70 °C |
| Maximum ambient temperature at power derating | +150 °C | +150 °C |
| Thermal shock | ± 0.25 % | ± 0.10 % |
| Low temperature operation | ± 0.25 % | ± 0.01 % |
| Short time overload | ± 0.5 % | ± 0.2 % |
| High temperature exposure | ± 0.2 % | ± 0.05 % |
| Resistance to soldering heat | ± 0.25 % | ± 0.025 % |
| Moisture resistance | ± 0.4 % | ± 0.01 % |
| Life at +70 °C for 1000 h | ± 1.00 % | ± 0.4 % |

Note


⁽¹⁾ Environmental testing was performed based on MIL-STD-202 standard test methods

| DIMENSIONS in inches | | | | | |
|----------------------|-------------------------|---------------|-------------------------------|-------------------------|-----------------|
| | | | | | |
| CASE SIZE | LENGTH L | WIDTH W | THICKNESS T MIN. / MAX. | TOP PAD D | BOTTOM PAD E |
| 0603 | 0.064 ± 0.006 | 0.032 ± 0.005 | 0.015 ± 0.003 | 0.012 ± 0.005 | 0.021 ± 0.005 |
| 0805 | 0.080 ± 0.006 | 0.050 ± 0.005 | 0.015 ± 0.003 | 0.016 ± 0.005 | 0.025 ± 0.005 |
| 1206 | 0.126 ± 0.008 | 0.063 ± 0.005 | 0.015 ± 0.003 | 0.020 + 0.005 / - 0.010 | 0.040 ± 0.005 |
| 2512 | 0.259 + 0.009 / - 0.015 | 0.124 ± 0.005 | 0.015 ± 0.003 | 0.020 ± 0.005 | 0.050 ± 0.005 |

| LAND PATTERN DIMENSIONS in inches | |
|-----------------------------------|---------------------------------|
| <p>0603 Land Pattern</p> | <p>1206 Land Pattern</p> |
| <p>0805 Land Pattern</p> | <p>2512 Land Pattern</p> |




| STANDARD MATERIAL SPECIFICATIONS | |
|----------------------------------|---|
| Resistive element | Passivated nichrome |
| Substrate material | Aluminum nitride |
| Terminations (tin/lead) | Tin / lead solder over nickel barrier |
| Terminations (lead (Pb)-free) | Tin / silver / copper (Sn96.5 / Ag3.0 / Cu0.5) solder over nickel barrier |




Note

- Chip surface temperature measured using FLIR SC645 thermal imaging system with an approximate testcard surface temperature of 75 °C




Note

- Chip surface temperature measured using FLIR SC645 thermal imaging system with an approximate testcard surface temperature of 75 °C



Note


- Chip surface temperature measured using FLIR SC645 thermal imaging system with an approximate test card surface temperature of 85 °C
- Thermal imaging was conducted under ambient conditions resulting in a steady state test card surface temperature of 85 °C over the full range of power levels
- Thermal imaging and load life testing was conducted mounting one device to a 1.6" x 3.7" test card with 3.5 mil copper plating on both surfaces. Thermal vias on 50 mil centers were utilized for heat transfer between surfaces of the test card




Note

- Chip surface temperature measured using FLIR SC645 thermal imaging system with an approximate test card surface temperature of 85 °C

DERATING CURVE



SINGLE PULSE LOAD TESTING



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: PCAN1206H1000BBT1

P C A N 1 2 0 6 H 1 0 0 0 B B T 1

| GLOBAL MODEL | CASE SIZE | TCR CHARACTERISTIC | RESISTANCE | TOLERANCE | TERMINATION | PACKAGING |
|--------------|------------------------------|--|--|---|---|---|
| PCAN | 0603 0805 1206 2512 | E = ± 25 ppm/°C H = ± 50 ppm/°C K = ± 100 ppm/°C (1) | The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. "R" designates the decimal point. Example: 10R0 = 10 Ω 1000 = 100 Ω | B = ± 0.1 % (2) C = ± 0.25 % D = ± 0.5 % F = ± 1.0 % (1) G = ± 2.0 % J = ± 5.0 % | B = wraparound Sn/Pb solder w/ nickel barrier S = wraparound lead (Pb)-free solder (e1) RoHS compliant G = wraparound Au, over Ni (gold) termination epoxy bondable RoHS compliant (e4) | BS = BULK 100 min., 1 mult. WS = WAFFLE 100 min., 1 mult. W0 = 100 pc min. waffle, 1 mult. W1 = 100 min., 1 mult. (package unit single lot date code) TAPE AND REEL T0 = 100 min., 100 mult. T1 = 1000 min., 1000 mult. T3 = 300 min., 300 mult. T5 = 500 min., 500 mult. TF = full reel TS = 100 min., 1 mult. TI = 100 min., 1 mult. (item single lot date code) TP = 100 min., 1 mult. (package unit single lot date code) |

Notes

- (1) Less than 10 Ω, 100 ppm/°C and 1 % tolerance best
- (2) Available on 10 Ω and higher



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.