

GDM-500 Series Hand-Held Digital Multimeter

GDM-541



GDM-533



GDM-532



GDM-531



FEATURES

GDM-541 FEATURES

- * 22000 Counts Auto/Manual Ranging
- * 46 Segments Analogue Bar
- * ACV Measurement up to 1000V
- * AC+DC Voltage Measurement
- * Current Measurement up to 20A
- * Transistor (hFE) Measurement
- * Audible/Visual Alarm when Overload
- * True RMS/USB Interface

GDM-533 FEATURES

- * 6000 Counts Auto/Manual Ranging
- * 31 Segments Analogue Bar
- * LoZ ACV Measurement
- * ACV Measurement up to 1000V
- * Current Measurement up to 20A
- * Temperature Measurement
- * Audible/Visual Alarm when Overload
- * True RMS/USB Interface

GDM-532 FEATURES

- * 9999 Counts Auto/Manual Ranging
- * Display Backlight/Auto Power Off
- * Continuity Beeper/Diode Test
- * Temperature Measurement
- * Non-Contact Voltage (NCV) Detection
- * Data Hold and Relative Mode

GDM-531 FEATURES

- * 6000 Counts Manual Ranging
- * Display Backlight/Auto Power Off
- * Capacitance Measurement
- * Non-Contact Voltage (NCV) Detection
- * Data Hold
- * Audible/Visual Alarm when Overload

The GDM-500 Series Hand Held DMM are a compact, high precision, battery operated multimeter series designed to meet of service engineers. The GDM-500 Series design is driven by mobile-oriented features: automatic power off to preserve battery life, a large backlight display for crisp viewing, a rotary selector and push buttons to ease operation, and then NCV (Non-Contact Voltage) function for outdoor use.

The basic functions match the depth of bench-top multimeters: fuse-protected current input, true RMS for accurate AC measurements, Audible/Visual Alarm when Overload, Auto ranging, Duty cycle and Relative mode. The compact, reliable and economical devices are ideal for any engineer.

SELECTION GUIDE

MODEL	GDM-541	GDM-533	GDM-532	GDM-531
Max. Display	22000	6000	9999	6000
Auto Ranging	✓	✓	✓	
Analogue Bar	✓	✓		
True RMS	✓	✓	✓	
Display Backlight	✓	✓	✓	✓
Auto Power off	✓	✓	✓	✓
Curr. Range Protection	PTS & Fuse	PTS & Fuse	Fuse	Fuse
DC Voltage	1000V	1000V	999.9V	600V
AC Voltage	1000V	1000V	999.9V	600V
DC Current	20A	20A	9.99A	10A
AC Current	20A	20A	9.99A	
Resistance	220MΩ	60MΩ	99.99MΩ	60MΩ
Capacitance	220mF	60mF	9.999mF	9.999mF
Frequency	220MHz	10MHz	9.9MHz	
Diode	✓	✓	✓	✓
Continuity	✓	✓	✓	✓
Temperature		✓	✓	
Duty Cycle (%)	✓	✓	✓	
Transistor (hFE)	✓			
NCV Function	✓	✓	✓	✓
REL	✓	✓	✓	
Data Hold	✓	✓	✓	✓
Peak Hold	✓	✓		
MAX MIN	✓	✓		
LoZ ACV		✓		
LPF ACV	✓			
Audible / Visual Alarm	✓	✓	✓	✓
AC+DC Measurement	✓			
Interface	USB	USB		
Safety Rating	CAT III 1000V CAT IV 600V	CAT III 1000V CAT IV 600V	CAT II 1000V CAT III 600V	CAT III 600V



Website



Facebook



LinkedIn

SPECIFICATIONS		
DC VOLTAGE	Range 220.00mV, 2.2000V, 22.000V, 220.00V, 1000V (GDM-541) 60.00mV, 600.0mV, 6.000V, 60.00V, 600.0V, 1000V (GDM-533) 9.999mV, 99.99mV, 999.9mV, 9.999V, 99.99V, 999.9V (GDM-532) 600.0mV, 6000mV, 60.00V, 600.0V (GDM-531) Best Accuracy $\pm(0.05\%rdg + 5 \text{ digits})$ for GDM-541; $\pm(0.5\%rdg + 3 \text{ digits})$ for GDM-533 $\pm(0.5\%rdg + 3 \text{ digits})$ for GDM-532; $\pm(0.7\%rdg + 3 \text{ digit})$ for GDM-531 Input Impedance 10 M Ω (At mV range : 1G Ω for GDM-541/533; 3G Ω for GDM-532)	
AC VOLTAGE	Range 220.00mV, 2.2000V, 22.000V, 220.00V, 1000.0V (GDM-541) 60.00mV, 600.0mV, 6.000V, 60.00V, 600.0V, 1000V (GDM-533) 9.999mV, 99.99mV, 999.9mV, 9.999V, 99.99V, 999.9V (GDM-532) 600.0V (GDM-531) Best Accuracy $\pm(0.8\%rdg + 10 \text{ digits})$ for GDM-541; $\pm(1.0\%rdg + 3 \text{ digits})$ for GDM-533 $\pm(0.8\%rdg + 3 \text{ digits})$ for GDM-532; $\pm(1.2\%rdg + 3 \text{ digits})$ for GDM-531 Frequency Response 40Hz-10kHz for GDM-541; 40Hz-1kHz for GDM-533 45Hz-400Hz for GDM-532; 40Hz-400Hz for GDM-531 Input Impedance 10 M Ω	
DC CURRENT	Range 220.00 μ A, 2200.0 μ A, 22.000mA, 220.00mA, 20.000A (GDM-541) 600.0 μ A, 6000 μ A, 60.00mA, 600.0mA, 6.000A, 20.00A (GDM-533) 999.9 μ A, 999.9mA, 9.999A (GDM-532) 600.0 μ A, 60.00mA, 600.0mA, 10.00A (GDM-531) Best Accuracy $\pm(0.5\%rdg + 10 \text{ digits})$ for GDM-541; $\pm(1.0\%rdg + 2 \text{ digits})$ for GDM-533 $\pm(0.8\%rdg + 3 \text{ digits})$ for GDM-532; $\pm(1.0\%rdg + 3 \text{ digits})$ for GDM-531	
AC CURRENT	Range 220.00 μ A, 2200.0 μ A, 22.000mA, 220.00mA, 20.000A (GDM-541) 600.0 μ A, 6000 μ A, 60.00mA, 600.0mA, 6.000A, 20.00A (GDM-533) 999.9 μ A, 999.9mA, 9.999A (GDM-532) Best Accuracy $\pm(0.8\%rdg + 10 \text{ digits})$ for GDM-541; $\pm(1.2\%rdg + 5 \text{ digits})$ for GDM-533 $\pm(1.0\%rdg + 3 \text{ digits})$ for GDM-532	
RESISTANCE	Range 220.00 Ω , 2.2000k Ω , 22.000k Ω , 220.00k Ω , 2.2000M Ω , 22.000M Ω , 220.00M Ω (GDM-541) 600.0 Ω , 6.000k Ω , 60.00k Ω , 600.0k Ω , 6.000M Ω , 60.00M Ω (GDM-533) 999.9 Ω , 9.999k Ω , 99.99k Ω , 999.9k Ω , 9.999M Ω , 99.99M Ω (GDM-532) 600.0 Ω , 6000 Ω , 60.00k Ω , 600.0k Ω , 60.00M Ω (GDM-531) Best Accuracy $\pm(0.5\%rdg + 10 \text{ digits})$ for GDM-541; $\pm(1.0\%rdg + 2 \text{ digit})$ for GDM-533 $\pm(0.8\%rdg + 2 \text{ digits})$ for GDM-532; $\pm(0.8\%rdg + 2 \text{ digits})$ for GDM-531	
CONTINUITY BEEPER	Buzzer sounds if conductance less than 50 Ω for GDM-541/533 Buzzer sounds if conductance less than 30 Ω for GDM-532 Buzzer sounds if conductance less than 10 Ω for GDM-531	
DIODE TEST	Open Circuit Voltage	GDM-541/533 : 3V (Approx.); GDM-532 : 3.3V (Approx.); GDM-531 : 2.1V (Approx.)
CAPACITANCE	Range 22.000nF, 220.00nF, 2.2000 μ F, 22.000 μ F, 220.00 μ F, 2.2000mF, 22.000mF, 220.00mF (GDM-461) 60.00nF, 600.0nF, 6.000 μ F, 60.00 μ F, 600.0 μ F, 6.000mF, 60.00mF (GDM-533) Best Accuracy 9.999nF, 99.99nF, 999.9nF, 9.999 μ F, 99.99 μ F, 999.9 μ F, 9.999mF (GDM-532/531) $\pm(3.0\%rdg + 5 \text{ digits})$ for GDM-541/533; $\pm(4.0\%rdg + 5 \text{ digits})$ for GDM-532/531	
FREQUENCY	Range 10Hz ~ 220MHz (GDM-541); 10Hz ~ 10MHz (GDM-533); 99.99Hz ~ 9.999MHz (GDM-532) Best Accuracy $\pm(0.01\%rdg + 5 \text{ digits})$ for GDM-541; $\pm(0.1\%rdg + 4 \text{ digits})$ for GDM-533 Input Amplitude $\pm(0.1\%rdg + 5 \text{ digits})$ for GDM-532 $\leq 20V_{rms}$	
TEMPERATURE	Range -40 $^{\circ}$ C ~ 1000 $^{\circ}$ C / -40 $^{\circ}$ F ~ 1832 $^{\circ}$ F Best Accuracy $\pm(1.0\%rdg + 3 \text{ }^{\circ}$ C) for GDM-533; $\pm(1.0\%rdg + 5 \text{ }^{\circ}$ C) for GDM-532 $\pm(1.0\%rdg + 4 \text{ }^{\circ}$ F) for GDM-533; $\pm(1.5\%rdg + 5 \text{ }^{\circ}$ F) for GDM-532	
SPECIAL FUNCTION	Auto Ranging (GDM-541/533/532); True RMS (GDM-541/533/532); Analog Bar (GDM-541/533); USB (GDM-541/533); Display Backlight (GDM-541/533/532/531); NCV Function (GDM-541/533/532/531); Audible/Visual Alarm (GDM-541/533/532/531); AC+DC Voltage (GDM-541); LPF ACV (GDM-541); hFE Test (GDM-541); LoZ ACV (GDM-533)	
LCD DISPLAY	22000 counts (GDM-541), 6000 counts (GDM-533/531), 9999 counts (GDM-532)	
POWER SOURCE	1.5V AAA x 4 (GDM-541/533); 1.5V AAA x 3 (GDM-532); 1.5V AAA x 2 (GDM-531)	
DIMENSIONS & WEIGHT	89(W) x 186(H) x 49(D) mm, Approx. 400g (GDM-541/533) 81(W) x 169(H) x 46(D) mm, Approx. 400g (GDM-532) 76.5(W) x 155(H) x 49(D) mm, Approx. 255g (GDM-531)	

GDM-500_E_D1DH_202205

ORDERING INFORMATION		ACCESSORIES
GDM-541	22000 Counts Hand-Held DMM with True RMS Measurement and USB Interface	User manual, Test leads, Battery,
GDM-533	6000 Counts Hand-Held DMM with True RMS Measurement and USB Interface	USB cable & Adapter socket (GDM-541/533 only),
GDM-532	9999 Counts Hand-Held DMM with True RMS Measurement	K-type thermocouple (GDM-533/532 only)
GDM-531	6000 Counts Hand-Held DMM	
		FREE DOWNLOAD
		GDM-541 PC Software Remote Software
		GDM-533 PC Software Remote Software

GOOD WILL INSTRUMENT CO., LTD.

No.7-1, Jhongsing Road, Tucheng Dist., New Taipei City 236, Taiwan

T +886-2-2268-0389 F +886-2-2268-0639

E-mail: marketing@goodwill.com.tw

GW INSTEK

Simply Reliable