



Part No. A1001312 Automotive Wi-Fi / BT / Zigbee or UWB Ceramic Antenna

2.4 GHz or 6.0 – 8.5 GHz

Supports: Wi-Fi applications, Agriculture, Automotive, Bluetooth, Zigbee, WLAN, Healthcare, UWB



*UWB layout offered in Appendix 1

Layouts:

1001312-01: Single Band 2.4 GHz 1001312-04: UWB 6.0 - 8.5 GHz (Appendix 1)

KEY BENEFITS		
Greater Flexibility with		
Unique Form Factors		Mechai
KYOCERA AVX' technology	helps	Orde
you deliver more advanced		
ergonomic designs without a	dverse	
impact on product performan	ice.	
Quicker Time-to-Market		
By optimizing antenna size,		
performance and emissions,		
customer and regulatory		
specifications are more easil	y met.	
AEC-Q200 Test Complete		
Reliability	•	Т
Products are the latest RoH	S	
version compliant.		
APPLICATIONS		Tem
Embedded • Telematics		
design • Tracking		
Smart Grid M2M		
OBD-II Industrial		

devices

UWB

KYOCERA AVX A-Series automotive antennas deliver on the key needs of device designers for higher functionality.

KYOCERA AVX has completed rigorous testing to qualify the A series antennas for automotive applications. This antenna has been AEC-Q200 tested. Customers must provide additional quality requirements, if any, to drive additional compliance testing.

Electrical Specifications

Typical performance on 55 x 25 mm PCB

Frequency	2400 – 2485 MHz	6.0 – 8.5 GHz	
Peak Gain	1.88 dBi	odix 1	
Average Efficiency	62%	ser to Appent	
VSWR Match	1.8:1 max	Reic	
Feed Point Impedance	50 ohn	ns unbalanced	
Polarization		Linear	
Power Handling	0.5	5 Watt CW	
Mechanical Specifications & Ordering Part Number			
Ordering Part Number		A1001312	
Size (mm)	2.00 x 1.20 x 0.55		
Mounting	Surface mounted to the PCB		
Weight (grams)	0.003		
Packaging	Tape & Reel A1001312 – 5,000 pieces per reel		
Demo Board	1001312-01 (2400 – 2485 MHz) 1001312-04 (UWB 6.0 – 8.5GHz		
Temperature Range	-5	-50/+125 °C	
Temperature Cycle	JESD22	D22 Method JA-104	
Temperature Exposure	MIL-STE	MIL-STD-202 Method 108	
High Temperature & High Humidity	MIL-STD-202 Method 103		
Mechanical Shock	MIL-STD-202 Method 213		
Vibration	MIL-STD-202 Method 204		
IMDS and PPAP available			

Proprietary



₿

2.4 GHz Automotive KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Antenna Dimensions

Part N

Typical antenna dimensions (mm)

		,		
	С	В	А	Part Number
	0.55 ± 0.2	1.2 ± 0.3	2.0 ± 0.3	A1001312
<u>View</u>	Top			





2.4 GHz Automotive KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs



Antenna Radiation Patterns

Typical performance on 55 x 25 mm PCB Measured @ 2440 MHz



© 2022 KYOCERA AVX

TDS-ANT-0094 | Rev 0



2.4 GHz Automotive KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs







BOTTOM METAL

TDS-ANT-0094 | Rev 0



2.4 GHz Automotive KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs

Antenna Demo Board

Typical layout dimensions (mm)

Part Number	Α	В	С
1001312-01	55.0	25.0	26.0



© 2022 KYOCERA AVX

TDS-ANT-0094 | Rev 0



Appendix 1 Automotive UWB KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

<u>Appendix 1</u>

Appendix 1 gives instructions on how to achieve UWB performances through layout and impedance matching network. (6.0 - 8.5 GHz)

Frequency (GHz)	6.0 - 8.5
Peak Gain	4.8 dBi
Average Efficiency	84%
VSWR Match	2.0:1 max
Feed Point Impedance	50 ohms unbalanced
Polarization	Linear
Power Handling	2 Watt CW

*Data shown above has Appendix 1 matching applied on 26.0 x 25.0 mm PCB, Using UWB 1001312-04 layout



© 2022 KYOCERA AVX

TDS-ANT-0094 | Rev 0



Appendix 1 Automotive UWB KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

VSWR and Efficiency Plots

Typical Performance on 26.0 x 25.0 mm PCB



Antenna Radiation Patterns

Typical performance on 26.0 x 25.0 mm PCB Measured @ 6500, 7000, 8000 MHz









012 Ζ

© 2022 KYOCERA AVX

TDS-ANT-0094 | Rev 0



Appendix 1 Automotive UWB KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.



		,
Component	Value	Tolerance
P1	DNI	N/A
S1	0Ω	N/A
P2	DNI	N/A

*Actual matching values depend on customer design







BOTTOM METAL

TDS-ANT-0094 | Rev 0



Appendix 1 Automotive UWB KYOCERA AVX Embedded Ceramic Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Antenna Demo Board

Typical layout dimensions (mm)



© 2022 KYOCERA AVX

TDS-ANT-0094 | Rev 0