



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Cannot be Certified**

Tooling Type: **SDE Crimp Die Set**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Tooling Type	SDE Crimp Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224)



Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 964201-1 STD TIMER CONTACT	 TE Part # CAT-T4827-T273 TIMER, RECEPTACLE AND TAB	 TE Part # 2392900-1 SDE F JR/STD TIMER 0.5-1.0mm2 ASSY	 TE Part # 964201-2 STD TIMER CONTACT
 TE Part # 927779-6 JPT REC 2.8 Contact SRC Ag (LP)	 TE Part # 927779-3 JPT REC 2.8 Contact SRC Sn (LP)	 TE Part # 927779-1 JPT REC 2.8 Contact SRC Sn (LP)	 TE Part # 927886-1 CI 2 BUCHSE
 TE Part # 927884-1 CI 2 STIFT	 TE Part # 927884-2 CI 2 STIFT	 TE Part # 927886-2 CI 2 BUCHSE	 TE Part # 1-963897-1 JUN-POW-TIM KONTAKT



 WIRE BARREL INSULATION BARREL TE Part # 1241823-1 STD TIMER CONTACT (LP)	 WIRE BARREL INSULATION BARREL TE Part # 1241823-2 STD TIMER CONTACT (LP)	 WIRE BARREL INSULATION BARREL TE Part # 1241823-3 STD TIMER CONTACT (LP)	TE Part # 2-963897-1 JUN-POW-TIM KONTAKT
 TE Part # 2362810-1 SDE CRIMP HAND TOOL FRAME W /O DIES	TE Part # 927885-2 CI 2 STIFT	TE Part # 927886-4 CI 2 BUCHSE	TE Part # 927887-2 CI 2 BUCHSE

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

SDE Crimp Commercial Tool System

English

Instruction Sheets

Instruction Sheet (U.S.)

English