


# Han Domino HD cube, crimp (M.1)



Part number	09 14 916 1001
Specification	Han Domino HD cube, crimp (M.1)
HARTING eCatalogue	https://b2b.harting.com/09149161001

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han <sup>®</sup> Domino High Density Cube
Size of the module	Domino module
Description of the module	Small tab

#### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	16
Details	Please order crimp contacts separately.

# Technical characteristics

Conductor cross-section	0.09 0.5 mm <sup>2</sup>
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000



### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

# Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

#### Commercial data

Packaging size	2
Net weight	3.98 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140185173
eCl@ss	27440217 Module for industrial connectors (power/signals)