

Right Angle Vertical Panel Mount Optopipe® Light Pipes

5mm Diameter Output


Features & Benefits

- Lengths varying from .250"–1.500"
- Flat, Convex and Domed lens options with diffused textured finish
- Designed for both single and multiple colored LEDs
- Precision molded from ROHS compliant UL94-V0. water clear polycarbonate with oxygen index of 35%
- Halogen-free PC material
- Optimally designed to be used with Dialight surface mount LEDs; see Surface Mount Selector Guide for LED options
- Recommend PLCC-2 and PLCC-4, surface mount LEDs part # 597-XXXX-207F

Application

Dialight's Right Angle Vertical Panel Mount Optopipe® Light Pipes provide an excellent solution for products that contain a PCB that is perpendicular to the front panel. The UL94-V0 water clear polycarbonate light pipes are secured to the front panel with a press fit that is easy to install. Dialight Optopipe® Light Pipes are a cost effective way of bringing indication to your front panel.

Dimensions



Mechanical Information

Mounting Hole Size: .156"± .002" Min. Panel Thickness: .063" (1.6 mm) **Operating Temp:** -40°C to +100°C Storage Temp: -40°C to +100°C



Ø .152 [3.86]

Rear View

Ø .140 [3.56]

Recommended Mounting hole



Ordering Information 515 Series

Flat

Dialight P/N Dim "C" 515-1361-0250F .190 [4.83] .165 [4.19] 515-1361-0350F .290 [7.37] .165 [4.19] 515-1361-0375F .165 [4.19] .315 [8.00] 515-1361-0500F .440 [11.18] .165 [4.19] 515-1361-0625F .565 [14.35] .165 [4.19] 515-1361-0750F .690 [17.53] .165 [4.19] 515-1361-0800F .740 [18.80] .165 [4.19] 515-1361-0900F .840 [21.34] .165 [4.19] 515-1361-1050F .990 [25.15] .165 [4.19] 515-1361-1250F 1.19 [30.23] .165 [4.19] 515-1361-1500F 1.44 [36.58] .165 [4.19]

Convex

Dialight P/N	Dim "1"	Dim "C"
515-1362-0250F	.190 [4.83]	.165 [4.19]
515-1362-0350F	.290 [7.37]	.165 [4.19]
515-1362-0375F	.315 [8.00]	.165 [4.19]
515-1362-0500F	.440 [11.18]	.165 [4.19]
515-1362-0625F	.565 [14.35]	.165 [4.19]
515-1362-0750F	.690 [17.53]	.165 [4.19]
515-1362-0800F	.740 [18.80]	.165 [4.19]
515-1362-0900F	.840 [21.34]	.165 [4.19]
515-1362-1050F	.990 [25.15]	.165 [4.19]
515-1362-1250F	1.19 [30.23]	.165 [4.19]
515-1362-1500F	1.44 [36.58]	.165 [4.19]

Domed

Dialight P/N	Dim "1"	Dim "C"
515-1363-0250F	.190 [4.83]	.165 [4.19]
515-1363-0350F	.290 [7.37]	.165 [4.19]
515-1363-0375F	.315 [8.00]	.165 [4.19]
515-1363-0500F	.440 [11.18]	.165 [4.19]
515-1363-0625F	.565 [14.35]	.165 [4.19]
515-1363-0750F	.690 [17.53]	.165 [4.19]
515-1363-0800F	.740 [18.80]	.165 [4.19]
515-1363-0900F	.840 [21.34]	.165 [4.19]
515-1363-1050F	.990 [25.15]	.165 [4.19]
515-1363-1250F	1.19 [30.23]	.165 [4.19]
515-1363-1500F	1.44 [36.58]	.165 [4.19]

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.