

AMP | AMP Superseal 1.5mm Series


TE Internal #: 282089-1

Housing for Female Terminals, Wire-to-Board / Wire-to-Wire / Wire-to-Device, 5 Position, .236 in [6 mm] Centerline, AMP Superseal 1.5 mm Series

View on TE.com >



Connectors > Automotive Connectors > Connector Housings > AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



Connector & Housing Type: Housing for Female Terminals

Mating Tab Width: 1.5 mm [.059 in]

Connector System: Wire-to-Board, Wire-to-Device, Wire-to-Wire

Number of Positions: 5

Centerline (Pitch): 6 mm [.236 in]

All AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING (26)

Features

Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to- Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	5
Number of Rows	1
Electrical Characteristics	
Operating Voltage	24 VDC
Nominal Voltage Architecture	12 V, 24 V
Body Features	
Cable Exit Angle	180°

PA GF

Body Material



Primary Product Color	Black
Connector Code	Neutral
Contact Features	
Contact Size	1.5mm
Contact Type	Receptacle
Mating Tab Width	1.5 mm[.059 in]
Contact Current Rating (Max)	14 A
Mechanical Attachment	
Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	Without
Mating Alignment Type	Polarization Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Centerline (Pitch)	6 mm[.236 in]
Dimensions	
Product Width	9.3 mm[.366 in]
Product Length	40.9 mm[1.61 in]
Product Height	32.2 mm[1.268 in]
Usage Conditions	
Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 - 125 °C[-40 - 257 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Degree of Protection	IP67
Packaging Features	
Packaging Quantity	400
	Bag



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts









10/13/2022 07:23AM | Page 3







Also in the Series | AMP Superseal 1.5mm Series



RECEPTACLE AND TAB

Automotive Connector Caps & Covers (2)



Automotive Housings(26)



Automotive Seals & Cavity Plugs(4)



Automotive Terminals(15)



Insertion & Extraction Tools(4)



Other Automotive Connector Accessories(2)

Documents

Product Drawings

AMP SUPERSEAL 1.5 SERIES 5P PL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_282089-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_282089-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_282089-1_D.3d_stp.zip

English



By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Datasheets & Catalog Pages

AMP SUPERSEAL 1.5mm Connector System

English

ICT Terminals and Connectors Catalogue

English

Product Specifications

Product Specification

English

Instruction Sheets

AMP SUPERSEAL 1.5 SERIES

English

Customer Manual (non U.S.)

English