



## Metal Working Tools - Chop Saws

D28700



### D28700 Features

- Horizontal handle for superior ergonomics and less user fatigue
- Spindle lock for quick and easy wheel change
- Quick release clamp results in less time in changing the work piece

### D28700 Specifications

Power Input	2200 Watts
Power Output	1350 Watts
No Load Speed	3800 rpm
Wheel Diameter	355 mm
Max. Cutting Capacity at 90° [Square Profile]	119 x 119 mm
Max. Cutting Capacity at 90° [Rectangular Profile]	115 x 130 mm
Max. Cutting Capacity at 90° [L-Shape Profile]	137 x 137 mm
Max. Cutting Capacity at 90° [Rounded Profile]	115 mm
Max. Cutting Capacity at 45° [Square Profile]	98 x 98 mm
Max. Cutting Capacity at 45° [Rectangular Profile]	115 x 98 mm
Max. Cutting Capacity at 45° [L-Shape Profile]	98 x 98 mm
Max. Cutting Capacity at 45° [Rounded Profile]	98 mm
Weight	16 kg
Length	486 mm
Height	378 mm

### D28700 Standard

- Metal cutting disc
- Hex key