swissbit®

Product Fact Sheet

Industrial e•MMC Memory

EM-36 Series

JEDEC e·MMC 5.1 compliant, BGA 100 ball, Enhanced Mode (pSLC)

Industrial Temperature Grade

Date: June 24, 2022

Revision: 1.00



Product Fact Sheet EM-36 Series



Product Summary

- Capacities: 5 GBytes, 10 GBytes, 20 GBytes, 40 GBytes, 80 GBytes
- Operating Temperature Range¹: Industrial Operating Temperature -40 to 85°C
- Endurance in TeraBytes Written (TBW) @ Max Capacity²: up to 2652

Product Features

- Fully compliant with JEDEC e·MMC 5.1 Standard (JESD84-B51)
- 100-ball BGA, 1.0mm pitch
- 14 x 18mm, RoHS compliant
- 3D TLC NAND base technology in Enhanced Mode (pSLC)
- Industrial Operating Temperature -40 to 85°C
- Single enhanced mode partition
- High performance e·MMC 5.1 specification
 - Eleven-wire bus (clock, Data Strobe, 1 bit command, 8 bit data bus) and a hardware reset
 - o Three different data bus width modes: 1-bit (default), 4-bit, and 8-bit
 - Clock frequencies o-200MHz, High Speed Mode HS400
 - o Command Queue Feature according to e∙MMC Spec 5.1
 - o Up to 300MB/s sequential read and up to 230MB/s sequential write
- Power Supply: (Low-power CMOS technology)
 - VCCQ 1.7V...1.95V or 2.7V...3.6V e•MMC supply
 - VCC 2.7V...3.6V NAND Flash supply
- Optimized FW algorithms
 - Power-fail data loss protection
 - Wear Leveling technology
 - Equal wear leveling of static and dynamic data. The wear leveling assures that dynamic data as well as static data is balanced evenly across the memory. With that the maximum write endurance of the device is ensured
 - o Read Disturb Management
 - The read commands per region are monitored and the content is conditionally refreshed when critical levels have occurred
 - Auto Read Refresh
 - The interruptible background process maintains the user data for Read Disturb effects or Retention degradation due to high temperature effects
 - Diagnostic features with Device Health Report according to e·MMC Spec 5.1, and detailed
 Lifetime Monitor data (Swissbit proprietary, accessible through standard e·MMC commands).
 - o Field Firmware update³ according to e∙MMC Spec 5.1
 - o Discard and Sanitize, Trim
 - o Boot Operation Mode and Alternative Boot Operation Mode
 - Replay Protected Memory Block (RPMB)
- High reliability
 - Designed with sophisticated firmware architecture for industrial and embedded markets.
 - Enhanced Mode (pSLC) with higher write performance and endurance than 3D TLC configured products (EM-30).
 - Ideal for application like POS/POI, PLC, IoT, gaming, medical and use as general boot medium for embedded applications.
 - The product is optimized for long life cycle that requires superior data retention as well as power fail safety.
 - Controlled BOM & PCN process



















Adequate airflow is required to ensure the temperature does not exceed 85°C (industrial temperature drive)

² According to JEDEC (JESD47I), the time to write the full TBW is a minimum of 18 months. Higher average daily data volume reduces the specified TBW. The values listed are estimates and are subject to change without notice.

³ The support of In-Field FW update capabilities on host systems is recommended.

Product Fact Sheet EM-36 Series



1 Order Information for EM-36

Density	Part Number	Industrial Temp. Range	Flash Technology	
5GB	SFEMoo5GB1ED1TO-I-5E-31P-STD	-40°C to 85°C	FW1: default	3D TLC NAND Flash in pSLC Mode
10GB	SFEM010GB1ED1T0-I-5E-31P-STD			
20GB	SFEM020GB1ED1T0-I-6F-31P-STD			
40GB	SFEM040GB1ED1T0-I-7G-31P-STD			
8oGB	SFEM080GB1ED1T0-I-8H-31P-STD			

1.1 System Performance

System Performance, HS400	Max. reliable mode	Unit
Burst Data transfer Rate HS400 (max clock 200MHz)	400	
Sequential Read	up to 300	MB/s
Sequential Write	up to 230	

1.2 Current Consumption

Current Consumption, HS400, Max. Density	Typ. ICCQ current @ VCCQ 1.8V	Typ. ICC current @ VCC 3.3V	Unit
Write	99	97	
Read	138	108	mA
Sleep	0.07	0.07	

1.3 Physical Dimensions

Physical Dimensions	Value	Unit
Length	18±0.1	mm
Width	14±0.1	
Thickness	1.4 max.	

1.4 Recommended Temperature Conditions

Parameter	Min.	Тур.	Max.	Unit
Industrial Operating / Storage Temperature	-40	25	85*	°C

^{*} High temperature storage without operation reduces the data retention, in operation the data will be refreshed, if data error issues were detected

For more information on e·MMC interface, please visit JEDEC homepage (www.jedec.org)

Why Swissbit?

Swissbit is focused on the design, development, manufacture, and support of leading edge memory and storage solutions for the worldwide OEM/ODM marketplace. As a global supplier, Swissbit recognizes and addressees the higher level of application requirements of today's industrial, Netcom, and automotive customers by providing best-in-class products and services, with uncompromised attention to driving overall value and quality.

