

ECG.1B.305.CLN

SUMMARY

Wires

Low voltage

5



Image is for illustrative purpose only

Series	1B	Download		
Termination type	Female print PCB	Request a quote		
IP rating	50	PCB Eagle Pattern		
AWG wire size	30.00 - 22.00	PCB Altium Pattern		
Cable Ø	0.00 - 0.00 mm	PCB KiCad Pattern		
Status	active	Catalog		
Matching parts	FGG.1B.305.CLAD52Z			

TECHNICAL DETAILS

Mechanics

Shell Style/Model	EC*: Fixed receptacle with two nuts and straight contacts for printed circuit (back panel mounting)
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight	10.46 g
Performance	
Configuration	1B.305 : 5 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	9 Amps

Specifications


Contact Type: Print (straight) Contact Dia.: 0.9 mm (0.035in) R (max): 4.8 mOhm Vtest (contact-shell): 1150 V (AC), 1630 V (DC) Vtest (contact-contact): 1250 V (AC), 1770 V (DC)


Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): 5000 Temp (min / max): -55°C / +250°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS







Dimensions

	А	В	E	Lmax	Μ	Nmax	S1	S3	e
mm.	16	15.8	6	22.9	3.5	19.5	10.5	14	M12x1.0
in.	0,63	0,62	0,24	0,90	0,14	0,77	0,41	0,55	

RECOMMENDED BY LEMO

Tools

Spanner 2:

DCH.91.161.PA

Spanner wrench:

Socket for torque wrench DCM.1S.M12.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.