

# EPL.00.250.NTD

## SUMMARY

#### # Wires

Coax	1	
		Image is for illustrative purpose only
Series	00	Download
Termination type	Male print PCB	Request a quote
IP rating	50	PCB Eagle Pattern
AWG wire size	0.00 - 0.00	PCB Altium Pattern
Cable Ø	0.00 - 0.00 mm	PCB KiCad Pattern
Status	active	Catalog

### **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model	EPL*: Elbow receptacle for printed circuit		
Keying	Circular, male		
Housing Material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces		
Weight	4.21 g		

#### Performance

Configuration	00.250 : 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated Current	4 Amps

#### **Specifications**

Contact Type: Coaxial 50 Ohm (Printed Circuit Board) Contact Dia.: 0.7 mm (0.028in) Test voltage: 2.1 kV (rms) R (max): 6.1 mOhm Vtest: 2100 V (AC), 3000 V (DC)


Impedance: 50 Ohm VSWR: 1.09 + 0.11 \* f/GHz

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

#### Others

Endurance (Shell): 5000 mating cycles F ret (min): 100 N Salt Spray Corrosion: >144 hr

### DRAWINGS





#### Dimensions

	А	н	L
mm.	7	10	17.5
in.	0,28	0,39	0,69

## **RECOMMENDED BY LEMO**

#### Tools

Spanner wrench:

Socket for torque wrench DCM.00.M07.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.