

2500-2700 MHz 12 dBi Gain Omnidirectional PRO Series Antenna - Type N Female Connector, Fiberglass Radome

HG2612U-PRO



Features

- All weather operation
- Includes heavy duty steel mast mounting brackets
- Lightweight fiberglass radome
- Integral N-Female connector
- 360° Omnidirectional Pattern

Applications

- 2500, 2600 Band Operation
- Point to Multipoint and Non Line of Sight (NLOS) Applications
- 12 dBi gain

Description

The L-com HG2612U-PRO is a high performance 5G / LTE outdoor omnidirectional antenna specifically designed for cellular networks. L-com's HG2612U-PRO has 12 dBi gain and can be used to broadcast Cellular LTE signals. The HG2612U-PRO operates from 2500 to 2700 MHz which is ideal for 5G, LTE, applications. The Multi-Band design of the L-com HG2612U-PRO antenna eliminates the need to purchase different antennas for each frequency. This simplifies installations since the same antenna can be used for a wide array of telecommunication applications where wide coverage is desired.

The HG2612U-PRO from L-com has omnidirectional patterns with vertical polarization and features Type N connectors. The Type N connectorized HG2612U-PRO antenna from L-com is designed specifically for outdoor operation and is ideal for point to multipoint use in large open areas such as base station installations or large campuses. The included mounting bracket and hardware makes this antenna very easy to install. This 5G / LTE outdoor omnidirectional antenna just like our wide selection of superior quality RF parts, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

Configuration

Design	Omni
Band Type	Single
Radiation Pattern	Directional
Polarization	Vertical
Connector Type	N Female
Number of Ports	2
Lightning Protection	DC Ground

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,500		2,700	MHz
Input VSWR		1.5:1		
Impedance		50		Ohms
Gain			12	
Input Power			50	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[2500-2700 MHz 12 dBi Omni Antenna, N Female, PRO Series, fiberglass radome HG2612U-PRO](#)

2500-2700 MHz 12 dBi Gain Omnidirectional PRO Series
Antenna - Type N Female Connector, Fiberglass Radome

HG2612U-PRO



Mechanical Specifications

Radome Material	Fiberglass
Size	
Length	46.45669 in [118 cm]
Width	1.37795 in [35 mm]
Height	1.37795 in [35 mm]
Mounting Mast Diameter	1.18 to 2.36 in [29.97 to 59.94 mm]
Weight	4.19 lbs [1.9 kg]

Environmental Specifications

Temperature	
Operating Range	-40 to +60 deg C
Wind Survivability	134.216 MPH [216 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2500-2700 MHz 12 dBi Gain Omnidirectional PRO Series Antenna - Type N Female Connector, Fiberglass Radome from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

T-Rev.D