


LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Exposed Junction thermocouple with Moulded on Miniature Type K IEC Plug





thermocouple connectors.

We are the largest UK manufacturer of both temperature sensors and

About Labfacility
Formed in 1971, Labfacility
specialize in the field of
Temperature and Process

Measurement.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email sales@labfacility.com

Website
www.labfacility.com

- PFA Teflon® twin twisted pair cable terminating with a moulded on type K IEC/ANSI miniature thermocouple plug
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
- Thermocouple type K
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- IEC584 or ANSI MC96.1 Colour Coded
- Ideal for test & development applications

T/C	Conductors	Length		Colour	Order Code
'K' 'K'	1/0.3mm 1/0.3mm	1 metres 2 metres	IEC IEC	Green / White Green / White	XF-1844-FAR XF-1842-FAR
'K' 'K'	1/0.3mm 1/0.5mm	3 metres 1 metres	IEC IEC	Green / White Green / White	XF-1830-FAR XF-1841-FAR
'K' 'K'	1/0.5mm 1/0.5mm	2 metres 3 metres	IEC IEC	Green / White Green / White	XF-1850-FAR XF-1242-FAR
'K' 'K' 'K'	1/0.3mm 1/0.3mm 1/0.3mm	1 metres 2 metres 3 metres	ANSI ANSI ANSI	Red / Yellow Red / Yellow Red / Yellow	XF-1849-FAR XF-1852-FAR XF-1837-FAR

