Model P09x Series









Features:

- Multi-ganged—up to 8 gangs
- Excellent 100,000 cycles life
- **Rotary and Momentary Switch options**
- **Push-lock options**
- Concentric shaft option
- Centre tap option
- PCB pins



Description:

9mm Rotary Potentiometer, with metal shaft and bushing. Options include audio and linear tapers; knurled, flatted and slotted shafts.

Applications:

- Audio / video equipment / Amplifiers / Mixers
- TV and multimedia sound systems / Portable electronics

Model Styles Available:

•	Side Adjust, 1 to 8 gangs	P09xN
•	Side Adjust, 1 to 4 gangs, w/Rotary switch	P09xS
•	Side Adjust, 1 to 4 gangs, w/Momentary switch	P09xM
•	Top Adjust, 1 or 2 gangs	P09x5N
•	Side Adjust, with Push-Lock, 1 or 2 gangs	P09xP
•	With Concentric shaft, 2 to 4 gangs	P09xC
•	With Centre Tap, 2 gangs only	P09xT

Electrical Characteristics

T_A = 25°C unless otherwise noted

Resistance Range	1KΩ to 1MΩ			
Standard Resistance Tolerance	± 20%			
Residual Resistance	20 ohms max			
Resistance Taper	Audio (10A, 15A, 15C), Linear (1B) - see note 3			
Maximum Operating Voltage	50Vac			
Rated Power	Linear Taper B: 0.05W			
Rated Power	Other Tapers: 0.025W			
Dielectric Strength	300 Vac , 1 minute			
Rotational Noise	100mV max			
Insulation Resistance	>100M ohms at 250 Vdc			
Gang Error (Multi-ganged)	-40dB to 0dB, ±3dB			

Model P09x Series



Switch Characteristics

T_A = 25°C unless otherwise noted

Switch Circuit	SPST
Contact Resistance	<100mohms
Rated Power	3.0A at 16Vdc
Switch Life	15,000 cycles min.

Mechanical Characteristics

T_A = 25°C unless otherwise noted

Mechanical Travel (Rotational angle)	300° ± 10°
Rotational Torque	35 to 90 gf.cm
Rotational Stop Strength, Minimum	3.0kgf.cm
Shaft Pull Strength, Minimum	6.0 kgf
Detent Torque	50 to 200 gf.cm
Nut Tightening Strength, Minimum	8.0 kgf
Rotational Life	100,000 cycles

Environmental Characteristics


T_A = 25°C unless otherwise noted

Operating Temperature	-10°C to 70°C
IP Rating	IP50
	Compatible with Industry standard soldering processes:
Soldering Condition	Manual: SAC 270 °C max. for 3 seconds.
	Wave: SAC 260 °C max. for 5 seconds.
RoHS	Please refer to TT Electronics Website
REACH	Please refer to TT Electronics Website

Model P09x Series



Ordering Information



Resistance table										
Resistance (Ohms)	1,000	2,000	5,000	10,000	20,000	50,000	100,000	200,000	500,000	1,000,000
Code	1K	2K	5K	10K	20K	50K	100K	200K	500K	1MEG


(see Note 1)

Model P09x Series




Note 1: Shaft type and Length


Shaft Types: P09xN, P09xS, P09x5N, P09xT




Shaft Types: P09xP (Push-Lock)



Shaft Types: P09xM (Momentary Switch)



Shaft Types: P09xC (Concentric Shafts)



Model P09x Series




Note 2: Shaft Position

Models: P09xN, P09xS, P09xM, P09x5N, P09xP, P09xT

F Shaft Type


FULL C.C.W Position Type A B C FULL CCW POSITION D 30°±10° FULL CCW POSITION D 30°±10° FULL CCW POSITION

E/Q Shaft Type




Models: P09xC

F Shaft Type



E/Q Shaft Type




Model P09x Series




Outline Drawings

Model P09xN (Side Adjust, PCB pins, up to 8 gangs)



Model P09xS and P09xM (Side Adjust, PCB pins, up to 4 gangs with Switch)




Model P09x Series




Outline Drawings

Model P09x5N (Top Adjust, PCB pins, up to 2 gangs)



Model P09xP (Side Adjust, PCB pins, with Push-Lock, up to 2 gangs)




Model P09x Series



Outline Drawings

Model P09xC (Side Adjust, PCB pins with Concentric Shaft, 2 to 4 gangs)




CIRCUIT DIAGRAM


Model P09x Series




Outline Drawings

Model P09xT (Side Adjust, PCB pins, with Center Tap, 2 gangs only)










Panel Layout





Model P09x Series




Note 3: Standard Tapers









Packaging

Standard Packaging	Plastic Trays
Hardware	Two flat washers and mounting nut