# **LINDSTRÖM®**

#### **RX 8140**

ERGO™ Micro-Bevel® Precision Cut Diagonal Cutter with Oval Head 0.2-1.25 mm




### PRODUCT DETAILS

- $\bullet$  Precision oval head diagonal cutters developed according to the scientific ERGOTM process, Oval head
- ERGO™ handles with two-component combination, thermoplastic surface, for comfortable grip, on tough polypropylene core for rigidity
- Micro-bevel, flush & ultra-cut
- The cutting capacity that is given is for copper wire
- Cutting capacity: 0.1 mm-0.8 mm to 0.4 mm-2 mm
- High performance alloyed steel
- Burnished finish

- Numerically controlled machine grinding guarantees edge angle accuracy & contact, increases the tool's reliability & consistency
- Precision induction-hardened edges 63-65 HRC
- Screw joint minimises friction & maximises alignment of cutting edges
- ESD safe handles in two-component synthetic material
- Bio spring limits the tension throughout the working cycle of the tool & can be adjusted to 3 different positions or removed
- Ideal for wire harness work & standard printed circuit board assembly





## PRODUCT ATTRIBUTES

#### Product: RX 8140 Oval S Micro-Bevel ® ₩<sub>0</sub> 0.2-1.25 mm 0.00-0.05 in 0.2-0.5 mm ₩, 0.01-0.02 in 135.5 mm 5.33 in 10,5 mm 0,41 in 10 mm 0.39 in 6 mm 0,24 inch 0,8 mm 0,03 in g 70 g Dissipative