




8163

**Micro-Bevel® Precision Cut
Diagonal Cutter with Tapered
Head & ESD Safe Handle 0.4-2 mm**



PRODUCT DETAILS

- 80 series precision diagonal cutters with tapered head
- ESD safe mono-material handles with return spring
- Micro-bevel, flush & ultra-flush cut
- The stated cutting capacity is for copper wire
- Suitable for cutting copper
- High performance alloy steel
- Burnished finish
- Numerically controlled machine grinding ensures edge angle accuracy and contact, increasing tool reliability and consistency
- Precision induction hardened edges 63-65 HRC
- Screw joint minimises friction and maximises alignment of cutting edges
- Ideal for assembly work where accessibility is a consideration
- CO standard handle shape in conductive material



PRODUCT ATTRIBUTES

Product: **8163**

	Tapered		L		Micro-Bevel ®
	0.4-2.0 mm		0.02-0.08 in		0.3-0.6 mm
	0.01-0.02 in	A	125 mm	A	4.92 in
B	16 mm	B	0,63 in	C	16 mm
C	0.63 in	D	8 mm	D	0,31 inch
F	1,6 mm	F	0,06 in		88 g
Ω	Dissipative				