# Programmable DC Electronic Loads multicomp PRO



### Description

These intelligent programmable DC single-channel electronic loads, are suitable for middle, low-power, and high-power applications. It uses a liquid crystal LCD panel display interface and an embedded spreadsheet, which is very simple operations and a clear man-machine interface.

#### Features

- Dynamic mode: up to 10kHz
- Resolution of voltage and current: 0.1mV/0.1mA
- · Waveform display function of voltage and current
- U disk storage of waveform data
- Interface: LAN, USB and RS232
- Four working modes: CV/CC/CR/CP

- Remote sensing function
- Battery test, automatic test, OPP test, OCP test functions
- Storage for 100 sets
- Short-circuit function
- Current monitoring function
- Power off memory function
- With rotary coding switch to make an easy operation

### Specification

Model		MP710771		MP710772		MP710773		MP710778		
	POWER	300W		500W		1000W		1500W		
Input Rating	Voltage	0-150V								
	Current	0-40A				0-40A				
CC Mode	Range	0-3A	0-40A	0-3A	0-40A	0-3A	0-40A	0-3A	0-40A	
	Resolution	0.1mA	1mA	0.1mA	1mA	0.1mA	1mA	0.1mA	1mA	
	Accuracy	±(0.05%of set+0.045%off.s)								
CV Mode	Range	0-18V	0-150V	0-18V	0-150V	0-18V	0-150V	0-50V	0-150V	
	Resolution	0.1mV	1mV	0.1mV	1mV	0.1mV	1mV	0.1mV	1mV	
	Accuracy	±(0.05%of set+0.025%off.s)								
CR Mode	Range	0.05Ω- 10Ω	10Ω- 7.5KΩ	0.05Ω- 10Ω	10Ω- 7.5KΩ	0.05Ω- 10Ω	10Ω- 7.5KΩ	0.05Ω- 10Ω	10Ω- 7.5KΩ	
	Resolution	16 bit								
	Accuracy	±(0.05%of set+0.025%off.s)								

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



# Programmable DC Electronic Loads Multicomp PRO

Model		MP710771		MP710772		MP710773		MP710778		
CW Mode	Range	300W		500W		1000W		1500W		
	Resolution	0.01W								
	Accuracy	±(0.1%of set+0.1%off.s)								
Slope	Range	0-3A	0-40A	0-3A	0-40A	0-3A	0-60A	0-3A	0-60A	
	Rising	0.0001- 0.3A/us	0.001- 1.5A/us	0.0001- 0.3A/us	0.001- 1.5A/us	0.0001- 0.3A/us	0.001-2A/ us	0.0001- 0.3A/us	0.001-2A/ us	
	Falling	0.0001- 0.3A/us	0.001- 1.5A/us	0.0001- 0.3A/us	0.001- 1.5A/us	0.0001- 0.3A/us	0.001-2A/ us	0.0001- 0.3A/us	0.001-2A/ us	
Voltage measurement	Range	0-18V	0-150V	0-18V	0-150V	0-18V	0-150V	0-18V	0-150V	
	Resolution	0.1mV	1mV	0.1mV	1mV	0.1mV	1mV	0.1mV	1mV	
	Accuracy	±(0.03%of set+0.025%off.s)								
Current measurement	Range	0-3A	0-40A	0-3A	0-40A	0-3A	0-60A	0-3A	0-60A	
	Resolution	0.1mA	1mA	0.1mA	1mA	0.1mA	1mA	0.1mA	1mA	
	Accuracy	±(0.05%of set+0.045%off.s)								
Power measurement	Range	300W		500W		1000W		1500W		
	Resolution	0.01W								
	Accuracy	±(0.1%of set+0.1%off.s)								
Over power protection		320W 52		0W 10		20W	1550W			
Over current protection		42A				62A				
Over voltage protection		155V								
Over temperature protection		85°C								
Input impedance		150ΚΩ								
Dimension (W × D × H)		215mm × 388mm × 15.5mm				430mm × 388mm × 150.5mm				

#### **Standard Warranty: 12 Months**

Accessories Included: EU/UK Power Cord, User Manual, Software CD, USB Cable, and RS232 Cable.

### Part Number Table

Description	Part Number		
Programmable DC Electronic Load, 300W	MP710771		
Programmable DC Electronic Load, 500W	MP710772		
Programmable DC Electronic Load, 1000W	MP710773		
Programmable DC Electronic Load, 1500W	MP710778		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet sheet sheet sheet hold check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

