

LQW18CN4N9D0H#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQW18CN4N9D0H# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQW18CN4N9D0H%23

"#" indicates a package specification code.

For Power Choke



















< List of part numbers with package codes >

LQW18CN4N9D0HB


LQW18CN4N9D0HD


LQW18CN4N9D0HJ



Appearance & Shape







(in mm)



References

Packaging	Specifications	Standard Packing Quantity
В	Bulk(Bag)	500
D	180mm Paper Tape	4000
J	330mm Paper Tape	10000

Mass (typ.)		
1 piece	0.004g	

1 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.





LQW18CN4N9D0H#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQW18CN4N9D0H# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQW18CN4N9D0H%23

"#" indicates a package specification code.



Specifications

L size	1.6±0.15mm
W size	0.8±0.15mm
T size	0.8±0.15mm
Size code inch (mm)	0603 (1608)
Inductance	4.9nH±0.5nH
Inductance Test Frequency	10MHz
Rated current (Itemp) (Based on Temperature rise)	2600mA
Max. of DC resistance	0.015Ω
Class of magnetic shield	No Shield
Self resonance frequency (min.)	2300MHz
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 125°C
Brand	Murata
Series	LQW18CN_0H

2 of 4

Attentior

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.





LQW18CN4N9D0H#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQW18CN4N9D0H# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQW18CN4N9D0H%23

"#" indicates a package specification code.




Notice For General

In operating temperatures exceeding +85°C, derating of current is necessary for this series.

Please apply the derating curve shown in the chart according to the operating temperature.

Derating of Rated Current



3 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.



Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of LQW18CN4N9D0H# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQW18CN4N9D0H%23


"#" indicates a package specification code.


LQW18CN4N9D0H#




Characteristic Data

The charts below may show another part number which shares its characteristics.







4 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

