

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200688282](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) In-Line Splitter, 4-Pole Male to 2 x 4-Pole Female, 22 AWG, 0.80m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|--|
| Product Family | Industrial Tees and Splitters |
| Series | 120068 |
| IP Rating | IP67 |
| Overview | Brad Micro-Change (M12) Connectors |
| Product Name | Micro-Change (M12) |
| Taxonomy | Industrial Tees and Splitters |
| Type | Splitter - In-line |
| UPC | 193264044610 |

Physical

| | |
|-------------------------------|---------------------|
| Color - Cable Jacket | Black |
| Drop Connector | N/A |
| Drop Gender | Male |
| Keyway | Single |
| LED Indicator | No |
| Left Trunk Connector | Micro-Change (M12) |
| Left Trunk Gender | Male |
| Leg 1 Length | 0.30m |
| Leg 2 Length | 0.50m |
| Material - Cable Jacket | TPU |
| Material - Connector Body | TPE |
| Material - Coupling Nut | Nickel-plated Brass |
| Net Weight | 61.198/g |
| Poles | 4 |
| Right Trunk Connector | Micro-Change (M12) |
| Right Trunk Gender | Female |
| Temperature Range - Operating | -20°C to +80°C |

Electrical


| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 60V |

Material Info

| | |
|--------------------|---------------|
| Engineering Number | 884A30B30M003 |
|--------------------|---------------|

Reference - Drawing Numbers

| | |
|---------------|-------------------|
| Sales Drawing | SD-120068-002-001 |
|---------------|-------------------|



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000385859_00_000.pdf

Declaration of Conformity

ZZCERT_UKCA

CER_4000410293_00_000.pdf

- Declaration of Conformity

Search Parts in this Series

[120068 Series](#)