

Straight Blade Devices

20 Amp, 125 Volt, 2-Pole, 3-Wire

inVIEW Illuminated Hospital Grade Devices

HUBBELL

Features

- Face LED Indicator
- Audible SNAP, indicates solid connection
- Reduces Installation Time
- Tamper-Resistant

Ordering Information

Description	UPC Number	Catalog Number
S-CONNECT DUP HG 20A/125V LED TR IV	783585250175	SNAP8300ILTR

Listings

UL
CSA

Specifications


Top	Polycarbonate
Base	Nylon
Contacts	Brass
Bridge	Galvanized Steel
Mounting Screws	Zinc Plated Steel

Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current

Mechanical	
Product Identification	Ratings are a permanent part of the device

Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

