

## Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

## inVIEW Illuminated Hospital Grade Devices

# HUBBELL

### Features

- Face LED Indicator
- Audible SNAP, indicates solid connection
- Reduces Installation Time
- Tamper-Resistant

### Ordering Information

Description	UPC Number	Catalog Number
S-CONNECT DUP HG 15A/125V LED TR RD	783585250403	SNAP8200RLTR

### Listings

UL  
CSA

### Specifications


Top	Polycarbonate
Base	Nylon
Contacts	Brass
Bridge	Galvanized Steel
Mounting Screws	Zinc Plated Steel

### Performance

Electrical	
Dielectric Voltage	Withstands 2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Mechanical	
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



15A 125V AC  
NEMA 5-15R  
UL CSA  
0.5 HP



### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

