53TP SERIES | IP00

PANEL MOUNT



Features

• Three-phase solid-state relay; Ratings 25 A, 50 A per phase @ 48-530 VAC

Sensata

Technologies

- 2 package styles IPO0 or IP20 (See IP20 spec sheet for more information)
- SCR output for heavy industrial loads
- Transient protection built in
- AC or DC control
- Zero-crossing (resistive loads) or random-fire (inductive loads) output
- LED input status indicator
- UL Recognized, CE Compliant to EN60950-1



PRODUCT SELECTION

Control Voltage	25 A	50 A
90-280 VAC	A53TP25D	A53TP50D
4-32 VDC	D 53TP25D	D53TP50D

SI

SPECIFICATIONS

AC Output ⁽¹⁾

1		
Description	25 A	50 A
Operating Voltage (47-63Hz) [Vrms]	48-530	48-530
Transient Overvoltage [Vpk] ²	1200	1200
Maximum Off-State Leakage Current @ Rated Voltage [mArms]	10	10
Minimum Off-State dv/dt @ Maximum Rated Voltage [V/sec] ³	500	500
Maximum Load Current [Arms] ⁴	25	50
Minimum Load Current [Arms]	0.05	0.05
Maximum Surge Current 50-60 Hz (16.6ms) [Apk]	239/250	597/625
Maximum On-State Voltage Drop @ Rated Current [Vpk]	1.6	1.6
Thermal Resistance Junction to Case (Rjc) [°C/W]	1.02	0.63
Maximum I ² t for Fusing 50-60 Hz (8.3 msec) [A ² sec]	285/260	1779/1620
Minimum Power Factor (with Maximum Load)	0.5	0.5



Page 1

Input ⁽¹⁾


Description	D53	A53			
Control Voltage Range	4-32 VDC	90-280 Vrms			
Minimum Turn-On Voltage	4.0 VDC	90 Vrms			
Minimum Turn-Off Voltage	1.0 VDC	10 Vrms			
Minimum Input Current (for on-state)	19 mA @ 4V	2.2 mA @ 120V			
Maximum Input Current	25 mA @ 32V	10mA @ 240V			
Nominal Input Impedance	Current Limiter	Current Limiter			
Maximum Turn-On Time [msec] ⁵	1/2 Cycle	50			
Maximum Turn-Off Time [msec]	1/2 Cycle	50			


General (1)

Description	Parameters
Dielectric Strength, Input/Output/Base (50/60Hz)	4000 Vrms
Minimum Insulation Resistance (@ 500 V DC)	10º Ohms
Maximum Capacitance, Input/Output	8 pF
Ambient Operating Temperature Range	-40°C to 80°C
Ambient Storage Temperature Range	-40°C to 125°C
Weight (typical)	10.3 oz (315g)
Encapsulation	Thermally conductive Epoxy
Terminals	Nickel plated Brass
Screws and Saddle clamps	Zinc plated Steel
Input Terminal Screw Torque Range:[in lbs/Nm]	8-10 / 0.9-1.1
Output Terminal Screw Torque Range:[in lbs/Nm]	15-20 / 1.7-2.2

P


THERMAL DERATE INFORMATION


















	Α	53TP	25	D	- [H	-1	0
Control Voltage -								
D: DC (4-32V) A: AC (90-280V)								
Series								
53TP								
Load Current —								
25: 25 Amps 50: 50 Amps								
Thermal Pad —								
Blank: Not Included H: Included								
Switching Mode								

- Required for valid part number

For options only and not required for valid part



⁽¹⁾All parameters at 25°C unless otherwise specified.

⁽²⁾ Relay will self trigger between 900-1200 Vpk.

- ⁽³⁾ Off-State dv/dt test method per EIA/NARM standard RS-443, paragraph 13.11.1
- ⁽⁴⁾ Heat sinking required, see page 4 for derating curves.
- ⁽⁵⁾ Turn-on time for Random turn-on versions is 0.02 msec (DC Control Models)



Page 4



Input: EN61000-4-2, Level 3 ESD EN61000-4-4, Level 3 Burst

Output: EN61000-4-2, Level 4 ESD EN61000-4-4, Level 4 Burst EN61000-4-5, Level 4 Surge EN60950: Meets the requirements of sections 1.5: 1,7 : 2.9: 2.10.5.3: 4.2: 4.5: 4.7:







WARNINGS



RISK OF MATERIAL DAMAGE AND HOT ENCLOSURE

- The product's side panels may be hot, allow the product to cool before touching
- · Follow proper mounting instructions including torque values
- Do not allow liquids or foreign objects to enter this product

Failure to follow these instructions can result in serious injury, or equipment damage.



HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power before installing or working with this equipment
- Verify all connections and replace all covers before turning on power

Failure to follow these instructions will result in death or serious injury.

Page 5

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS. NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

+1 (877) 502 5500

+44 (1202) 416170

Asia Pacific

ext 2808

sales.crydom@sensata.com

ssr-info.eu@sensata.com

China +86 (21) 2306 1500

Japan +81 (45) 277 7117

Korea +82 (31) 601 2004

India +91 (80) 67920890

Europe, Middle East & Africa

sales.isasia@list.sensata.com

Rest of Asia +886 (2) 27602006

Americas