

August 2016

Multilayer Diplexer

For 2400-2500MHz / 5150-5850MHz

DPX105850DT-6019A1

1.0x0.5mm [EIA 0402]*


* Dimensions Code JIS[EIA]


Multilayer Diplexer

For 2400-2500MHz / 5150-5850MHz

DPX105850DT-6019A1

SHAPES AND DIMENSIONS






Terminal functions		
1	Common	
2	GND	
3	High-band	
4	Low-band	


Dimensions in mm

RECOMMENDED LAND PATTERN



Dimensions in mm

EVALUATION BOARD



Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

Conformity to RoHS Directive

ELECTRICAL CHARACTERISTICS

LOW-BAND

ltem	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	2400 to 2500	—	0.30	0.50
Return Loss (dB)	2400 to 2500	10	18	—
Attenuetion (dP)	4800 to 6000	18	24	_
Attenuation (dB)	7200 to 7500	15	21	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

HIGH-BAND

ltem	Frequenc (MHz)	y Range	Min.	Тур.	Max.
Insertion Loss (dB)	5150 to	5850		1.04	1.50
Return Loss (dB)	5150 to	5850	10	15	—
	700 to	2025	27	37	_
	2400 to	2690	35	40	_
Attenuation (dB)	3500 to	3700	10	14	_
	7250 to	7800	11	15	_
	10300 to 1	1700	20	28	_
Characteristic Impedance (Ω)				50 (Nominal)	

• Ta: +25±5°C

ltem	Frequency Range (MHz)	Min.	Тур.	Max.
Baturn Loop (dB)	2400 to 2500	10	19	—
Return Loss (dB)	5150 to 5850	10	14	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

TEMPERATURE RANGE


Operating temperature	Storage temperature
(°C)	(°C)
-40 to +85	-40 to +85

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.


DPX105850DT-6019A1

FREQUENCY CHARACTERISTICS


LOW-BAND




Return Loss











Return Loss



Attenuation




• All specifications are subject to change without notice.


• Before using these products, be sure to request the delivery specifications.

DPX105850DT-6019A1

FREQUENCY CHARACTERISTICS








All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) Peak Temp. Time Temp. Time Temp. Time T1 T2 **T**4 t1 ТЗ t2 t3* 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30sec max.

*t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

▲ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.