

RF Attenuator
6607_SMA-50-3/199_N
Description

Standard Attenuator Low Power



Product Configuration

Connector (side 1 / side 2)	SMA plug (male) / SMA jack (female)
Interface Standards	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data	
Nominal impedance	50 Ω
Nominal attenuation	7 dB
Frequency range	DC to 27 GHz
Attenuation deviation (±dB)	0.65
VSWR max.	1.3
Power rating	2 Watt average power up to 25 °C ambient temperature, linearly derated to 0.2 Watt at 100 °C ambient temperature. 250 Watt peak power, 5 µs pulse, 0.4 % duty cycle

Mechanical Data

Weight	0.005 kg
--------	----------

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Part (side 1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	Passivated (Plating)
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-01166140
-----------------	--------------

Ordering Information

85177156	6607_SMA-50-3/199_NE
----------	----------------------