

LAN Transformer 10/100 Base-T PoE

Part No: TM2019ANL

Description:

10/100 Base-T transformer Single Port and 16pin SMT with PoE

Features:

PoE (350mA) Industrial grade RoHS & REACH Compliant



1.	Introduction	3
2.	Specifications	4
3.	Mechanical	5
4.	Electrical	6
5.	Packaging & Storage	7
	Changelog	8

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













1. Introduction



Featuring a compatible footprint with industry LAN transformers, and designed to work in demanding industrial environmental conditions, the Taoglas TM2019ANL is a LAN Transformer 10/100Base-T Single Port of 16pins that is capable to work in industrial environmental conditions.

Typical applications for this cost-effective part are:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

The Taoglas Magnetics Product Team have over fifteen years of LAN magnetics design and high-quality manufacturing. With an ever-expanding portfolio, we provide trusted products and services to customers within a wide range of applications such as: Networking and Interconnect Devices, Servers, Switches, Router, Communication systems and any Digital Consumer electronics.

The Taoglas Exos Series offer an extensive product line of LAN Transformers designed for commercial and industrial grade applications, supporting 10/100 Base-T (Exos100 Series), 1G Base-T (Exos1G Series) and 10G Base-T (Exos10G Series). These products include Single, Dual, and Quad configurations not only for standard applications but also for Power over Ethernet (PoE, PoE+, PoE++).

For more information on the range of products or for assistance with integration, contact your regional Taoglas customer support team.



2. Specifications

Electrical Performance @25°C					
Inductance OCL	350μH MIN @ 100KHz 0.1V 8mA DC Bias				
Turns Ratio (±2%)	TX=1CT: 1CT	RX=1CT: 1CT			
DCR	1-3,6-8:1.2ΩMax				
Leakage Inductance	1-3 (Tie:16+14): 0.5uH Max @ 100KHz 0.1				
	6-8 (Tie:11+9): 0.5uF	H Max @ 100KHz 0.1V			
Cw/w	(1-3) to (16-14): 28pf	F Max @ 100KHz 0.1V			
	(6-8) to (11-9): 28pF	Max @ 100KHz 0.1V			
Insertion Loss	-1.4dB MAX @	@ 0.1-100Mhz			
	-16dB MIN	@ 0-30Mhz			
Return Loss	-14dB MIN (@ 30-40Mhz			
	-13dB MIN @ 40-50Mhz				
	-12dB MIN (@ 50-80Mhz			
	-45dB MIN	@ 0-30Mhz			
Cross talk	-40dB MIN (@ 30-40Mhz			
	-35dB MIN @	9 60-100Mhz			
DCMR (dB MIN)	-43dB MIN	@ 0-30Mhz			
	-37dB MIN (@ 30-60Mhz			
	-33dB MIN @	9 60-100Mhz			
Hi-Pot	1500Vr	rms Min			

Environmental Specifications				
Operating Temperature	-40°C TO +85°C			


Compliance
UL recognized - FILE NO. E528697
RoHS Compliant


Storage requirements			
Humidity	Storage Temperature		
MSL - 1	-40°C TO +85°C		



3. Mechanical

3.1 Mechanical Drawings






Mechanical Specifications				
Length	12.7 mm			
Width	9.45 mm			
Height	4.95 mm			
Mounting Style	Surface Mount (SMT)			

Dimensions are in millimeters with the following tolerances: $X.XX = \pm 0.25$

3.2 Pad Layout




 $\label{eq:Suggested Pad Layout}$ Dimensions are in millimeters with the following tolerances: X.XX = ± 0.10




4. Electrical

4.1 Electrical Drawings



4.2 Profile of Reflow Solder





5. Packaging and Storage

5.1 SPQ


1300 pcs/reel

A (Carrier Tape Width): 24±0.3 mm

B (Sprocket hole to Cavity center): 11.5±0.2 mm

C (Cavity width): 10.45±0.2 mm


Reel weight: 750 g



1CTN = 6 reels = 3900 pcs


Carton dimensions: 370*370*250mm

Carton Weight: 6.5 kg





Changelog







www.taoglas.com

