

## PRODUCT SPECIFICATION

### MT-7029N Noise-filtering Network PoE Toner & Probe Kit



\*\*\* Picture for reference only. All specifications are subject to change by supplier. \*\*\*

#### Specifications:

MT-7029N Transmitter specifications	
Wire tracing	RJ45 Lan cable Cat5, 5e, 6, 7 (UTP/STP), RJ11/12 telephone cable
	Voltage 8Vp-p
	Frequency 455KHz
	Tracing distance 600m
Cable mapping	RJ45 Test/Scan socket for RJ45 locating Individual wire pairs
	RJ11 POL/Scan socket for RJ11 locating Individual wire pairs
	8+1 LED indicators.
Crimping Test	Test distance max.: 300m
	For RJ45, RJ11/RJ12 plug
Port Flash	8 LED indicators
Telephone line POL +/-	1 LED indicator
Auto power off	1 dual color LED: POL- (Green) / POL+ (Red)
Low battery indication	1 hour
Voltage protection	About 7.0V; power indicator will flash.
Battery	DC 60V
Working current	9V (NEDA 1604/6F22) x1pcs
Dimension	Tracing/Cable map/Crimping <35mA; Port flash <110mA
Weight	L138 x W80 x D35mm
	142g
MT-7029N Receiver Specifications	
Frequency	455KHz
Tracing indication	1 LED indicator & speaker
Cable mapping	RJ45 socket

Cable map indication	8+1 LED indicators
NCV	1 LED indicator & speaker (AC 90-1000V)
Earphone	Φ 3.5mm socket
Lighting	1 LED
Low battery indication	About 7.0V; power indicator will flash.
Battery	9V (NEDA 1604/6F22) x1pcs
Working current	Tracing <200mA; lighting<50mA
Dimension	L203 x W50 x D32mm
weight	95g
Accessories	RJ45 cable patch cords x2, RJ11 cable patch cords x2, RJ11 to alligator clips patch cord x1, earphone x1, storage bag, user manual.

**Product Weight (w/o package) :**

Weight(Kg)	Measurement		
0.47	L(mm)	W(mm)	H(mm)
	260	130	80

**Individual Packing**

Packing: Color Box

**Master Packing :**

	Pcs	N. W (Kg)	G. W (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.47	26	13	8	-
Inner Box							-
CTN	20	9.2	10.2	46.5	28	45	2.07

**~ THE END ~**